

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262508

Luminaire Tested: P3AS09R709727DE010 E3DLP1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262508  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R709727DE010 E3DLP1LI  
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 440.0 lumens  
Efficiency: N/A  
Efficacy: 39.6 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262508  
CATALOG NUMBER: P3AS09R709727DE010 E3DLP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1262508  
 CATALOG NUMBER: P3AS09R709727DE010 E3DLP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46				46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	103215
5°	101320
10°	95523
15°	86697
20°	75840
25°	63971
30°	52388
35°	40636
40°	29083
45°	18421
50°	9177
55°	5620
60°	4824
65°	4462
70°	3911
75°	3643
80°	3031
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18421 cd/sqm



TEST NUMBER: P1262508  
 CATALOG NUMBER: P3AS09R709727DE010 E3DLP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.9	9.8
10°-20°	106.3	24.2
20°-30°	121.0	27.5
30°-40°	94.6	21.5
40°-50°	46.5	10.6
50°-60°	14.3	3.2
60°-70°	8.5	1.9
70°-80°	4.5	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.2	61.4
0°-40°	364.9	82.9
0°-60°	425.7	96.8
0°-90°	440.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	440.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	471	
5°	460	43
15°	382	106
25°	264	121
35°	152	95
45°	59	46
55°	15	14
65°	9	8
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1262508  
CATALOG NUMBER: P3AS09R709727DE010 E3DLP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	470.7
2.5°	468.2
5°	460.3
7.5°	447.4
10°	429.0
12.5°	407.6
15°	381.9
17.5°	354.4
20°	325.0
22.5°	294.4
25°	264.4
27.5°	235.0
30°	206.9
32.5°	178.7
35°	151.8
37.5°	126.1
40°	101.6
42.5°	79.0
45°	59.4
47.5°	41.6
50°	26.9
52.5°	17.7
55°	14.7
57.5°	12.9
60°	11.0
62.5°	9.8
65°	8.6
67.5°	7.3
70°	6.1
72.5°	4.9
75°	4.3
77.5°	3.7
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)