

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262532

Luminaire Tested: P3AS10R129727DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262532  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS10R129727DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R12 optic, 2700K CCT AND, 97CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 603.0 lumens  
Efficiency: N/A  
Efficacy: 51.5 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262532  
CATALOG NUMBER: P3AS10R129727DE010 E3DL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1262532  
 CATALOG NUMBER: P3AS10R129727DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	515112
5°	457252
10°	317540
15°	187788
20°	106946
25°	61141
30°	33828
35°	18042
40°	9990
45°	5396
50°	3377
55°	2676
60°	2281
65°	2127
70°	1859
75°	1949
80°	1515
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5396 cd/sqm



TEST NUMBER: P1262532  
 CATALOG NUMBER: P3AS10R129727DE010 E3DL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.6	29.3
10°-20°	233.1	38.7
20°-30°	120.0	19.9
30°-40°	45.1	7.5
40°-50°	14.8	2.4
50°-60°	6.3	1.1
60°-70°	4.0	0.7
70°-80°	2.4	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.8	87.9
0°-40°	574.9	95.3
0°-60°	596.0	98.8
0°-90°	603.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	603.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2349	
5°	2077	177
15°	827	233
25°	253	120
35°	67	45
45°	17	15
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1262532  
CATALOG NUMBER: P3AS10R129727DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2349.1
1°	2344.5
2°	2313.7
3°	2255.0
4°	2177.8
5°	2077.3
6°	1963.4
7°	1838.5
8°	1699.7
9°	1562.6
10°	1426.1
12.5°	1097.3
15°	827.2
17.5°	619.2
20°	458.3
22.5°	342.1
25°	252.7
27.5°	184.1
30°	133.6
32.5°	94.7
35°	67.4
37.5°	48.2
40°	34.9
42.5°	25.0
45°	17.4
47.5°	12.8
50°	9.9
52.5°	8.1
55°	7.0
57.5°	5.8
60°	5.2
62.5°	4.6
65°	4.1
67.5°	3.5
70°	2.9
72.5°	2.9
75°	2.3
77.5°	1.7
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)