

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262539

Luminaire Tested: P3AS10R129727DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262539
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS10R129727DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 2700K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 458.0 lumens
Efficiency: N/A
Efficacy: 39.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262539

CATALOG NUMBER: P3AS10R129727DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1262539

CATALOG NUMBER: P3AS10R129727DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65		
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60		
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56		
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115517
5°	112392
10°	102715
15°	89966
20°	77170
25°	64431
30°	51578
35°	38682
40°	28081
45°	18358
50°	11496
55°	7761
60°	6885
65°	6330
70°	5963
75°	5422
80°	5177
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18358 cd/sqm

TEST NUMBER: P1262539

CATALOG NUMBER: P3AS10R129727DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.1	10.3
10°-20°	110.4	24.1
20°-30°	121.7	26.6
30°-40°	91.1	19.9
40°-50°	47.2	10.3
50°-60°	19.6	4.3
60°-70°	12.1	2.6
70°-80°	6.8	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.2	61.0
0°-40°	370.3	80.9
0°-60°	437.1	95.4
0°-90°	458.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	458.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	527	
5°	511	47
15°	396	110
25°	266	122
35°	144	91
45°	59	47
55°	20	20
65°	12	12
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1262539

CATALOG NUMBER: P3AS10R129727DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	526.8
1°	527.4
2°	525.7
3°	522.2
4°	517.0
5°	510.6
6°	502.5
7°	493.8
8°	483.3
9°	472.3
10°	461.3
12.5°	429.4
15°	396.3
17.5°	363.2
20°	330.7
22.5°	297.6
25°	266.3
27.5°	235.0
30°	203.7
32.5°	172.9
35°	144.5
37.5°	120.1
40°	98.1
42.5°	77.7
45°	59.2
47.5°	44.7
50°	33.7
52.5°	24.9
55°	20.3
57.5°	18.0
60°	15.7
62.5°	13.9
65°	12.2
67.5°	10.4
70°	9.3
72.5°	7.5
75°	6.4
77.5°	5.2
80°	4.1
82.5°	2.9
85°	1.7
87.5°	0.6
90°	0.0

(END OF REPORT)