

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261808

Luminaire Tested: P3AS05R159727DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159727DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 162.0 lumens
Efficiency: N/A
Efficacy: 22.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261808

CATALOG NUMBER: P3AS05R159727DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1261808

CATALOG NUMBER: P3AS05R159727DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	70	63	58	78	69	63	58	67	62	58		66	61	58		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40852
5°	39753
10°	36339
15°	31828
20°	27302
25°	22792
30°	18231
35°	13679
40°	9933
45°	6481
50°	4060
55°	2753
60°	2412
65°	2231
70°	2116
75°	1949
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6481 cd/sqm

TEST NUMBER: P1261808

CATALOG NUMBER: P3AS05R159727DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.7	10.3
10°-20°	39.1	24.1
20°-30°	43.0	26.6
30°-40°	32.2	19.9
40°-50°	16.7	10.3
50°-60°	6.9	4.3
60°-70°	4.3	2.6
70°-80°	2.4	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	98.8	61.0
0°-40°	131.0	80.9
0°-60°	154.6	95.4
0°-90°	162.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	162.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	186	
5°	181	17
15°	140	39
25°	94	43
35°	51	32
45°	21	17
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1261808

CATALOG NUMBER: P3AS05R159727DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	186.3
1°	186.6
2°	185.9
3°	184.7
4°	182.9
5°	180.6
6°	177.7
7°	174.6
8°	171.0
9°	167.1
10°	163.2
12.5°	151.9
15°	140.2
17.5°	128.5
20°	117.0
22.5°	105.3
25°	94.2
27.5°	83.1
30°	72.0
32.5°	61.2
35°	51.1
37.5°	42.5
40°	34.7
42.5°	27.5
45°	20.9
47.5°	15.8
50°	11.9
52.5°	8.8
55°	7.2
57.5°	6.4
60°	5.5
62.5°	4.9
65°	4.3
67.5°	3.7
70°	3.3
72.5°	2.7
75°	2.3
77.5°	1.8
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.2
90°	0.0

(END OF REPORT)