

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261818

Luminaire Tested: P3AS05R159727DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159727DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 435.0 lumens
Efficiency: N/A
Efficacy: 60.4 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261818
CATALOG NUMBER: P3AS05R159727DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1261818
 CATALOG NUMBER: P3AS05R159727DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94	93	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	90	88	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	87	86	85	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	82	81	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	80	79	78	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	77	76	75	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	74	73	72	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	72	71	70	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	68	67	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	66	65	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	371615
5°	329847
10°	229076
15°	135460
20°	77147
25°	44107
30°	24409
35°	13010
40°	7185
45°	3907
50°	2422
55°	1912
60°	1667
65°	1505
70°	1346
75°	1440
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3907 cd/sqm



TEST NUMBER: P1261818
 CATALOG NUMBER: P3AS05R159727DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.4	29.3
10°-20°	168.2	38.7
20°-30°	86.6	19.9
30°-40°	32.5	7.5
40°-50°	10.6	2.4
50°-60°	4.6	1.1
60°-70°	2.9	0.7
70°-80°	1.7	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	382.2	87.9
0°-40°	414.7	95.3
0°-60°	429.9	98.8
0°-90°	435.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	435.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1695	
5°	1498	127
15°	597	168
25°	182	87
35°	49	33
45°	13	11
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1261818
CATALOG NUMBER: P3AS05R159727DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1694.7
1°	1691.3
2°	1669.1
3°	1626.8
4°	1571.0
5°	1498.5
6°	1416.4
7°	1326.3
8°	1226.1
9°	1127.3
10°	1028.8
12.5°	791.6
15°	596.7
17.5°	446.7
20°	330.6
22.5°	246.8
25°	182.3
27.5°	132.8
30°	96.4
32.5°	68.3
35°	48.6
37.5°	34.8
40°	25.1
42.5°	18.0
45°	12.6
47.5°	9.2
50°	7.1
52.5°	5.9
55°	5.0
57.5°	4.2
60°	3.8
62.5°	3.4
65°	2.9
67.5°	2.5
70°	2.1
72.5°	2.1
75°	1.7
77.5°	1.3
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)