

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262546

Luminaire Tested: P3AS10R129727DE010 E3PHLP1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1262546  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS10R129727DE010 E3PHLP1MW  
Description: 3in Adjustable LED luminaire with, R12 optic, 2700K CCT AND, 97CRI , E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 317.0 lumens  
Efficiency: N/A  
Efficacy: 27.1 lumens/watt  
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262546

CATALOG NUMBER: P3AS10R129727DE010 E3PHLP1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1262546

CATALOG NUMBER: P3AS10R129727DE010 E3PHLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 100 | 102 | 99  | 97  |  | 98  | 96  | 94  |  | 95  |
| 2   | 105 | 99  | 94  | 90  | 102 | 97  | 92  | 89  | 94  | 90  | 87  |  | 91  | 87  | 85  |  | 88  |
| 3   | 99  | 91  | 85  | 80  | 96  | 89  | 84  | 80  | 87  | 82  | 78  |  | 84  | 80  | 77  |  | 82  |
| 4   | 93  | 84  | 78  | 73  | 91  | 83  | 77  | 72  | 81  | 76  | 71  |  | 79  | 74  | 71  |  | 77  |
| 5   | 88  | 78  | 72  | 67  | 86  | 77  | 71  | 67  | 76  | 70  | 66  |  | 74  | 69  | 65  |  | 72  |
| 6   | 83  | 73  | 67  | 62  | 82  | 73  | 66  | 62  | 71  | 65  | 61  |  | 70  | 65  | 61  |  | 68  |
| 7   | 79  | 69  | 62  | 58  | 78  | 68  | 62  | 58  | 67  | 61  | 57  |  | 66  | 61  | 57  |  | 65  |
| 8   | 75  | 65  | 59  | 54  | 74  | 65  | 58  | 54  | 63  | 58  | 54  |  | 62  | 57  | 54  |  | 61  |
| 9   | 72  | 62  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 55  | 51  |  | 59  | 54  | 51  |  | 58  |
| 10  | 69  | 59  | 52  | 48  | 68  | 58  | 52  | 48  | 57  | 52  | 48  |  | 56  | 51  | 48  |  | 56  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 118653 |
| 5°  | 108937 |
| 10° | 86794  |
| 15° | 64881  |
| 20° | 49261  |
| 25° | 37309  |
| 30° | 27599  |
| 35° | 19702  |
| 40° | 13482  |
| 45° | 9427   |
| 50° | 8051   |
| 55° | 7875   |
| 60° | 8201   |
| 65° | 8665   |
| 70° | 8784   |
| 75° | 9150   |
| 80° | 9976   |
| 85° | 9812   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 11592 cd/sqm

TEST NUMBER: P1262546

CATALOG NUMBER: P3AS10R129727DE010 E3PHLP1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 43.8   | 13.8      |
| 10°-20°   | 80.1   | 25.3      |
| 20°-30°   | 71.0   | 22.4      |
| 30°-40°   | 46.5   | 14.7      |
| 40°-50°   | 24.8   | 7.8       |
| 50°-60°   | 18.8   | 5.9       |
| 60°-70°   | 16.2   | 5.1       |
| 70°-80°   | 11.1   | 3.5       |
| 80°-90°   | 4.6    | 1.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 195.0  | 61.5      |
| 0°-40°    | 241.5  | 76.2      |
| 0°-60°    | 285.1  | 89.9      |
| 0°-90°    | 317.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 317.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 541 |      |
| 5°  | 495 | 44   |
| 15° | 286 | 80   |
| 25° | 154 | 71   |
| 35° | 74  | 46   |
| 45° | 30  | 25   |
| 55° | 21  | 19   |
| 65° | 17  | 16   |
| 75° | 11  | 11   |
| 85° | 4   | 5    |
| 90° | 0   |      |

TEST NUMBER: P1262546

CATALOG NUMBER: P3AS10R129727DE010 E3PHLP1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 541.1 |
| 2.5°  | 528.3 |
| 5°    | 494.9 |
| 7.5°  | 445.8 |
| 10°   | 389.8 |
| 12.5° | 335.8 |
| 15°   | 285.8 |
| 17.5° | 245.5 |
| 20°   | 211.1 |
| 22.5° | 180.7 |
| 25°   | 154.2 |
| 27.5° | 130.6 |
| 30°   | 109.0 |
| 32.5° | 90.3  |
| 35°   | 73.6  |
| 37.5° | 58.9  |
| 40°   | 47.1  |
| 42.5° | 37.3  |
| 45°   | 30.4  |
| 47.5° | 26.5  |
| 50°   | 23.6  |
| 52.5° | 22.6  |
| 55°   | 20.6  |
| 57.5° | 19.6  |
| 60°   | 18.7  |
| 62.5° | 17.7  |
| 65°   | 16.7  |
| 67.5° | 14.7  |
| 70°   | 13.7  |
| 72.5° | 11.8  |
| 75°   | 10.8  |
| 77.5° | 8.8   |
| 80°   | 7.9   |
| 82.5° | 6.9   |
| 85°   | 3.9   |
| 87.5° | 2.0   |
| 90°   | 0.0   |

(END OF REPORT)