

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262575

Luminaire Tested: P3AS13R129727DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R129727DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 2700K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 453.0 lumens
Efficiency: N/A
Efficacy: 29.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262575
CATALOG NUMBER: P3AS13R129727DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1262575
 CATALOG NUMBER: P3AS13R129727DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195335
5°	180541
10°	144130
15°	108877
20°	82911
25°	63173
30°	45273
35°	29526
40°	18120
45°	10947
50°	7266
55°	5620
60°	4824
65°	4203
70°	3783
75°	3728
80°	2778
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10947 cd/sqm



TEST NUMBER: P1262575
 CATALOG NUMBER: P3AS13R129727DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.7	16.0
10°-20°	134.0	29.6
20°-30°	119.4	26.3
30°-40°	70.6	15.6
40°-50°	29.0	6.4
50°-60°	13.6	3.0
60°-70°	8.3	1.8
70°-80°	4.3	1.0
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.1	72.0
0°-40°	396.7	87.6
0°-60°	439.2	97.0
0°-90°	453.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	453.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	891	
5°	820	73
15°	480	134
25°	261	119
35°	110	71
45°	35	29
55°	15	14
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1262575
CATALOG NUMBER: P3AS13R129727DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	890.8
1°	888.6
2°	882.0
3°	868.8
4°	846.7
5°	820.2
6°	791.5
7°	757.7
8°	722.4
9°	686.3
10°	647.3
12.5°	558.3
15°	479.6
17.5°	411.9
20°	355.3
22.5°	305.3
25°	261.1
27.5°	218.5
30°	178.8
32.5°	142.7
35°	110.3
37.5°	84.6
40°	63.3
42.5°	47.1
45°	35.3
47.5°	27.2
50°	21.3
52.5°	17.7
55°	14.7
57.5°	12.5
60°	11.0
62.5°	9.6
65°	8.1
67.5°	7.4
70°	5.9
72.5°	5.1
75°	4.4
77.5°	2.9
80°	2.2
82.5°	1.5
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)