

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261828

Luminaire Tested: P3AS05R209727DE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261828
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209727DE010 E3CD1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 97CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 528.9 lumens
Efficiency: N/A
Efficacy: 73.5 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261828
CATALOG NUMBER: P3AS05R209727DE010 E3CD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1261828

CATALOG NUMBER: P3AS05R209727DE010 E3CD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	98	98	98
2	112	109	107	104	110	108	105	103	104	103	101	102	100	99	99	98	97	97	98	97	95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	95	97	96	93
4	107	102	99	96	105	101	98	96	99	97	95	97	95	93	96	94	92	92	96	94	91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	91	94	92	90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	88	93	90	88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	86	91	89	86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	85	89	87	85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	83	88	86	83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	87	84	82	82	87	84	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	821601
5°	713117
10°	440629
15°	153054
20°	46997
25°	16622
30°	6153
35°	2463
40°	1317
45°	527
50°	273
55°	306
60°	351
65°	208
70°	256
75°	339
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 527 cd/sqm



TEST NUMBER: P1261828
 CATALOG NUMBER: P3AS05R209727DE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.9	50.8
10°-20°	213.3	40.3
20°-30°	36.9	7.0
30°-40°	6.7	1.3
40°-50°	1.5	0.3
50°-60°	0.7	0.1
60°-70°	0.4	0.1
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	519.2	98.2
0°-40°	525.9	99.4
0°-60°	528.1	99.8
0°-90°	528.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	528.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3747	
5°	3240	269
15°	674	213
25°	69	37
35°	9	7
45°	2	2
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1261828
CATALOG NUMBER: P3AS05R209727DE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3746.8
1°	3728.8
2°	3657.6
3°	3543.3
4°	3409.3
5°	3239.7
6°	3045.4
7°	2819.3
8°	2561.8
9°	2272.4
10°	1978.9
12.5°	1248.2
15°	674.2
17.5°	360.1
20°	201.4
22.5°	115.2
25°	68.7
27.5°	41.9
30°	24.3
32.5°	14.2
35°	9.2
37.5°	6.3
40°	4.6
42.5°	2.9
45°	1.7
47.5°	0.8
50°	0.8
52.5°	0.8
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)