

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261839

Luminaire Tested: P3AS05R209727DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209727DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 162.0 lumens
Efficiency: N/A
Efficacy: 22.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261839

CATALOG NUMBER: P3AS05R209727DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1261839

CATALOG NUMBER: P3AS05R209727DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40063
5°	39005
10°	35871
15°	31578
20°	27092
25°	22743
30°	18383
35°	14000
40°	9962
45°	6574
50°	4060
55°	2676
60°	2456
65°	2231
70°	2116
75°	1949
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6574 cd/sqm

TEST NUMBER: P1261839

CATALOG NUMBER: P3AS05R209727DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.4	10.1
10°-20°	38.7	23.9
20°-30°	43.0	26.5
30°-40°	32.8	20.2
40°-50°	16.8	10.4
50°-60°	6.9	4.3
60°-70°	4.3	2.6
70°-80°	2.4	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	98.1	60.5
0°-40°	130.9	80.8
0°-60°	154.6	95.4
0°-90°	162.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	162.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	183	
5°	177	16
15°	139	39
25°	94	43
35°	52	33
45°	21	17
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1261839

CATALOG NUMBER: P3AS05R209727DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	182.7
1°	182.9
2°	182.1
3°	181.1
4°	179.4
5°	177.2
6°	174.5
7°	171.6
8°	168.5
9°	164.8
10°	161.1
12.5°	150.4
15°	139.1
17.5°	127.6
20°	116.1
22.5°	104.5
25°	94.0
27.5°	83.5
30°	72.6
32.5°	62.4
35°	52.3
37.5°	43.4
40°	34.8
42.5°	27.4
45°	21.2
47.5°	16.1
50°	11.9
52.5°	8.8
55°	7.0
57.5°	6.4
60°	5.6
62.5°	4.9
65°	4.3
67.5°	3.7
70°	3.3
72.5°	2.7
75°	2.3
77.5°	1.9
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.2
90°	0.0

(END OF REPORT)