

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262618

Luminaire Tested: P3AS13R209727DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262618
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209727DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1020.0 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262618
CATALOG NUMBER: P3AS13R209727DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1262618
 CATALOG NUMBER: P3AS13R209727DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	100
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96	95	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93	93
4	106	101	98	95	105	100	97	95	99	96	94	97	95	93	95	93	92	91	91	91	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90	89	89	89	89
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	92	89	88	87	87	87	87
7	99	93	90	87	98	93	89	87	92	89	86	91	88	86	90	87	86	85	85	85	85
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84	83	83	83	83
9	95	89	85	83	94	89	85	83	88	85	83	87	84	83	87	84	82	81	81	81	81
10	93	87	84	81	92	87	83	81	86	83	81	86	83	81	85	83	81	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1547266
5°	1302726
10°	813679
15°	304202
20°	104426
25°	43527
30°	20509
35°	9182
40°	4351
45°	2233
50°	819
55°	153
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2233 cd/sqm



TEST NUMBER: P1262618
 CATALOG NUMBER: P3AS13R209727DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	492.2	48.2
10°-20°	405.4	39.7
20°-30°	92.1	9.0
30°-40°	23.5	2.3
40°-50°	5.9	0.6
50°-60°	0.7	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	989.7	97.0
0°-40°	1013.1	99.3
0°-60°	1019.8	100.0
0°-90°	1020.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1020.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7056	
5°	5918	492
15°	1340	405
25°	180	92
35°	34	23
45°	7	6
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1262618
CATALOG NUMBER: P3AS13R209727DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7056.1
1°	6996.2
2°	6820.0
3°	6567.1
4°	6256.9
5°	5918.3
6°	5541.0
7°	5124.6
8°	4638.9
9°	4157.5
10°	3654.3
11°	3118.7
12°	2583.9
13°	2130.8
14°	1697.7
15°	1340.0
16°	1057.6
17°	834.3
18°	670.4
19°	545.2
20°	447.5
21°	374.1
22°	312.3
23°	259.6
24°	216.6
25°	179.9
27.5°	117.6
30°	81.0
32.5°	49.9
35°	34.3
37.5°	21.9
40°	15.2
42.5°	10.4
45°	7.2
47.5°	4.8
50°	2.4
52.5°	1.2
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1262618
CATALOG NUMBER: P3AS13R209727DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)