

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262700

Luminaire Tested: P3AS13R309727DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309727DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 633.0 lumens
Efficiency: N/A
Efficacy: 43.4 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262700

CATALOG NUMBER: P3AS13R309727DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1262700

CATALOG NUMBER: P3AS13R309727DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94
2	104	98	93	88	102	96	91	87	93	89	85		90	86	83		87
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64
7	76	65	57	52	74	64	57	52	62	56	52		61	56	52		60
8	71	60	53	48	70	60	53	48	58	52	48		57	52	48		56
9	68	57	50	45	66	56	49	45	55	49	45		54	49	45		53
10	64	53	47	42	63	53	46	42	52	46	42		51	46	42		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	155974
5°	149086
10°	128588
15°	106584
20°	87368
25°	70431
30°	56768
35°	46498
40°	38644
45°	32748
50°	28042
55°	24238
60°	21621
65°	18887
70°	16541
75°	13895
80°	10355
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32748 cd/sqm

TEST NUMBER: P1262700

CATALOG NUMBER: P3AS13R309727DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	9.7
10°-20°	130.9	20.7
20°-30°	134.2	21.2
30°-40°	109.7	17.3
40°-50°	82.0	13.0
50°-60°	57.6	9.1
60°-70°	36.3	5.7
70°-80°	17.4	2.8
80°-90°	3.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.5	51.6
0°-40°	436.2	68.9
0°-60°	575.9	91.0
0°-90°	633.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	633.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	711	
5°	677	61
15°	470	131
25°	291	134
35°	174	110
45°	106	82
55°	63	58
65°	36	36
75°	16	17
85°	2	3
90°	0	

TEST NUMBER: P1262700

CATALOG NUMBER: P3AS13R309727DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	711.3
2.5°	704.3
5°	677.3
7.5°	632.7
10°	577.5
12.5°	523.5
15°	469.5
17.5°	420.2
20°	374.4
22.5°	331.0
25°	291.1
27.5°	255.9
30°	224.2
32.5°	198.4
35°	173.7
37.5°	153.8
40°	135.0
42.5°	119.7
45°	105.6
47.5°	92.7
50°	82.2
52.5°	72.8
55°	63.4
57.5°	56.3
60°	49.3
62.5°	42.3
65°	36.4
67.5°	30.5
70°	25.8
72.5°	21.1
75°	16.4
77.5°	11.7
80°	8.2
82.5°	4.7
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)