

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261951

Luminaire Tested: P3AS05R409727DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409727DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 587.0 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261951

CATALOG NUMBER: P3AS05R409727DE010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1261951

CATALOG NUMBER: P3AS05R409727DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96	95	94	92
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93	91	90	88
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90	88	86	85
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88	85	83	82
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85	82	80	79
7	93	86	81	78	92	85	81	78	84	80	77		83	80	77		82	79	77	76
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79	76	74	73
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77	74	71	70
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		75	71	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	299208
5°	297050
10°	289262
15°	258390
20°	171328
25°	64189
30°	17167
35°	6719
40°	2405
45°	1147
50°	341
55°	153
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1147 cd/sqm

TEST NUMBER: P1261951

CATALOG NUMBER: P3AS05R409727DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.3	21.7
10°-20°	301.6	51.4
20°-30°	136.8	23.3
30°-40°	17.7	3.0
40°-50°	3.1	0.5
50°-60°	0.4	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.7	96.4
0°-40°	583.4	99.4
0°-60°	586.8	100.0
0°-90°	587.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	587.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1364	
5°	1350	127
15°	1138	302
25°	265	137
35°	25	18
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1261951

CATALOG NUMBER: P3AS05R409727DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1364.5
1°	1363.7
2°	1361.6
3°	1358.5
4°	1354.6
5°	1349.5
6°	1343.5
7°	1336.1
8°	1327.1
9°	1314.8
10°	1299.1
11°	1280.9
12°	1256.4
13°	1226.2
14°	1186.7
15°	1138.2
16°	1076.4
17°	1005.9
18°	921.2
19°	831.8
20°	734.2
21°	636.6
22°	540.5
23°	444.7
24°	350.6
25°	265.3
26°	196.5
27°	143.8
28°	108.1
29°	84.0
30°	67.8
31°	56.1
32°	46.9
32.5°	42.7
33°	38.6
34°	31.4
35°	25.1
36°	19.7
37°	15.6
37.5°	14.0
38°	12.3
39°	10.3
40°	8.4
42.5°	5.5
45°	3.7



TEST NUMBER: P1261951

CATALOG NUMBER: P3AS05R409727DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.3
50°	1.0
52.5°	0.4
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)