

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262737

Luminaire Tested: P3AS13R409727DE010 E3D1LI

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1262737  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R409727DE010 E3D1LI  
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1139.0 lumens  
Efficiency: N/A  
Efficacy: 78.0 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262737

CATALOG NUMBER: P3AS13R409727DE010 E3D1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1262737

CATALOG NUMBER: P3AS13R409727DE010 E3D1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 112 | 110 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 |  | 103 | 102 | 101 |  | 99  |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98  |  | 99  | 97  | 96  |  | 96  |
| 3   | 107 | 102 | 98  | 95  | 105 | 100 | 97  | 94  | 98  | 95  | 93  |  | 96  | 93  | 91  |  | 93  |
| 4   | 103 | 97  | 93  | 90  | 101 | 96  | 92  | 89  | 94  | 91  | 88  |  | 92  | 89  | 87  |  | 90  |
| 5   | 99  | 93  | 89  | 85  | 98  | 92  | 88  | 85  | 91  | 87  | 84  |  | 89  | 86  | 84  |  | 88  |
| 6   | 96  | 89  | 85  | 81  | 95  | 89  | 84  | 81  | 87  | 83  | 81  |  | 86  | 83  | 80  |  | 85  |
| 7   | 93  | 86  | 81  | 78  | 92  | 85  | 81  | 78  | 84  | 80  | 77  |  | 83  | 80  | 77  |  | 82  |
| 8   | 90  | 83  | 78  | 75  | 89  | 82  | 78  | 75  | 81  | 77  | 75  |  | 80  | 77  | 74  |  | 79  |
| 9   | 87  | 80  | 75  | 72  | 86  | 79  | 75  | 72  | 78  | 75  | 72  |  | 78  | 74  | 72  |  | 77  |
| 10  | 84  | 77  | 72  | 70  | 83  | 77  | 72  | 69  | 76  | 72  | 69  |  | 75  | 72  | 69  |  | 74  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 580568 |
| 5°  | 576380 |
| 10° | 561290 |
| 15° | 501388 |
| 20° | 332459 |
| 25° | 124556 |
| 30° | 33322  |
| 35° | 13010  |
| 40° | 4666   |
| 45° | 2233   |
| 50° | 682    |
| 55° | 306    |
| 60° | 175    |
| 65° | 208    |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2233 cd/sqm

TEST NUMBER: P1262737

CATALOG NUMBER: P3AS13R409727DE010 E3D1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 247.1  | 21.7      |
| 10°-20°   | 585.2  | 51.4      |
| 20°-30°   | 265.4  | 23.3      |
| 30°-40°   | 34.4   | 3.0       |
| 40°-50°   | 6.0    | 0.5       |
| 50°-60°   | 0.7    | 0.1       |
| 60°-70°   | 0.2    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1097.7 | 96.4      |
| 0°-40°    | 1132.1 | 99.4      |
| 0°-60°    | 1138.8 | 100.0     |
| 0°-90°    | 1139.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1139.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2648 |      |
| 5°  | 2618 | 247  |
| 15° | 2209 | 585  |
| 25° | 515  | 265  |
| 35° | 49   | 34   |
| 45° | 7    | 6    |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1262737

CATALOG NUMBER: P3AS13R409727DE010 E3D1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2647.6 |
| 1°    | 2646.0 |
| 2°    | 2642.0 |
| 3°    | 2636.1 |
| 4°    | 2628.5 |
| 5°    | 2618.5 |
| 6°    | 2607.0 |
| 7°    | 2592.6 |
| 8°    | 2575.1 |
| 9°    | 2551.1 |
| 10°   | 2520.8 |
| 11°   | 2485.3 |
| 12°   | 2437.9 |
| 13°   | 2379.3 |
| 14°   | 2302.7 |
| 15°   | 2208.6 |
| 16°   | 2088.6 |
| 17°   | 1951.8 |
| 18°   | 1787.6 |
| 19°   | 1614.1 |
| 20°   | 1424.7 |
| 21°   | 1235.3 |
| 22°   | 1048.7 |
| 23°   | 862.9  |
| 24°   | 680.2  |
| 25°   | 514.8  |
| 26°   | 381.2  |
| 27°   | 279.1  |
| 28°   | 209.7  |
| 29°   | 163.1  |
| 30°   | 131.6  |
| 31°   | 108.9  |
| 32°   | 90.9   |
| 32.5° | 82.9   |
| 33°   | 75.0   |
| 34°   | 61.0   |
| 35°   | 48.6   |
| 36°   | 38.3   |
| 37°   | 30.3   |
| 37.5° | 27.1   |
| 38°   | 23.9   |
| 39°   | 19.9   |
| 40°   | 16.3   |
| 42.5° | 10.8   |
| 45°   | 7.2    |

TEST NUMBER: P1262737

CATALOG NUMBER: P3AS13R409727DE010 E3D1LI

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 47.5° | 4.4 |
| 50°   | 2.0 |
| 52.5° | 0.8 |
| 55°   | 0.8 |
| 57.5° | 0.4 |
| 60°   | 0.4 |
| 62.5° | 0.4 |
| 65°   | 0.4 |
| 67.5° | 0.0 |
| 70°   | 0.0 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)