

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261963

Luminaire Tested: P3AS05R409727DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409727DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 375.0 lumens
Efficiency: N/A
Efficacy: 52.1 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261963

CATALOG NUMBER: P3AS05R409727DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1261963

CATALOG NUMBER: P3AS05R409727DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84182
5°	82654
10°	77910
15°	70761
20°	62165
25°	53084
30°	43981
35°	33917
40°	24131
45°	16250
50°	8870
55°	6270
60°	5877
65°	5448
70°	4873
75°	4660
80°	3662
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16250 cd/sqm

TEST NUMBER: P1261963

CATALOG NUMBER: P3AS05R409727DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.0	9.3
10°-20°	86.8	23.2
20°-30°	100.4	26.8
30°-40°	79.1	21.1
40°-50°	40.6	10.8
50°-60°	15.5	4.1
60°-70°	10.3	2.7
70°-80°	5.6	1.5
80°-90°	1.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.2	59.3
0°-40°	301.4	80.4
0°-60°	357.5	95.3
0°-90°	375.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	375.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	384	
5°	376	35
15°	312	87
25°	219	100
35°	127	79
45°	52	41
55°	16	16
65°	10	10
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1261963

CATALOG NUMBER: P3AS05R409727DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	383.9
2.5°	381.8
5°	375.5
7.5°	364.6
10°	349.9
12.5°	332.7
15°	311.7
17.5°	289.9
20°	266.4
22.5°	242.5
25°	219.4
27.5°	196.4
30°	173.7
32.5°	150.6
35°	126.7
37.5°	104.5
40°	84.3
42.5°	67.1
45°	52.4
47.5°	38.2
50°	26.0
52.5°	18.9
55°	16.4
57.5°	14.7
60°	13.4
62.5°	11.7
65°	10.5
67.5°	8.8
70°	7.6
72.5°	6.3
75°	5.5
77.5°	4.2
80°	2.9
82.5°	2.5
85°	1.3
87.5°	0.8
90°	0.0

(END OF REPORT)