

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262765

Luminaire Tested: P3AS13R459727DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459727DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1091.0 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262765
CATALOG NUMBER: P3AS13R459727DE010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1262765
 CATALOG NUMBER: P3AS13R459727DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94	92	91
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	92	90	88	87
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87	92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	83	88	86	84	83
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	85	82	80	79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	82	79	76	75
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	79	76	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	473010
5°	475522
10°	460913
15°	386245
20°	295262
25°	179744
30°	74796
35°	23958
40°	7443
45°	1520
50°	1126
55°	1262
60°	1053
65°	1245
70°	1026
75°	1356
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1520 cd/sqm



TEST NUMBER: P1262765
 CATALOG NUMBER: P3AS13R459727DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.7	18.7
10°-20°	467.6	42.9
20°-30°	336.7	30.9
30°-40°	70.0	6.4
40°-50°	6.4	0.6
50°-60°	2.6	0.2
60°-70°	2.1	0.2
70°-80°	1.4	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1008.1	92.4
0°-40°	1078.1	98.8
0°-60°	1087.2	99.7
0°-90°	1091.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1091.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2157	
5°	2160	204
15°	1701	468
25°	743	337
35°	90	70
45°	5	6
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1262765
CATALOG NUMBER: P3AS13R459727DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2157.1
2.5°	2157.9
5°	2160.3
7.5°	2144.9
10°	2070.0
12.5°	1913.8
15°	1701.4
17.5°	1484.2
20°	1265.3
22.5°	1013.9
25°	742.9
27.5°	489.8
30°	295.4
32.5°	165.2
35°	89.5
37.5°	50.4
40°	26.0
42.5°	11.4
45°	4.9
47.5°	3.3
50°	3.3
52.5°	3.3
55°	3.3
57.5°	2.4
60°	2.4
62.5°	2.4
65°	2.4
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)