

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262004

Luminaire Tested: P3AS05R509727DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262004  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R509727DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 582.0 lumens  
Efficiency: N/A  
Efficacy: 80.8 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262004  
CATALOG NUMBER: P3AS05R509727DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1262004  
 CATALOG NUMBER: P3AS05R509727DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80	80	80	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68	68	68	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	65	65	65	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	59	59	59	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	203383
5°	197974
10°	188930
15°	171034
20°	147970
25°	121362
30°	69732
35°	21656
40°	5811
45°	2047
50°	478
55°	153
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2047 cd/sqm



TEST NUMBER: P1262004  
 CATALOG NUMBER: P3AS05R509727DE010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.2	14.5
10°-20°	208.8	35.9
20°-30°	219.4	37.7
30°-40°	62.8	10.8
40°-50°	6.1	1.1
50°-60°	0.5	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	512.4	88.0
0°-40°	575.2	98.8
0°-60°	581.8	100.0
0°-90°	582.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	582.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	928	
5°	899	84
15°	753	209
25°	502	219
35°	81	63
45°	7	6
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1262004  
CATALOG NUMBER: P3AS05R509727DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	927.5
1°	926.1
2°	922.0
3°	916.0
4°	908.0
5°	899.4
6°	890.1
7°	880.3
8°	871.0
9°	860.4
10°	848.5
11°	834.7
12°	818.9
13°	799.2
14°	777.8
15°	753.4
16°	727.5
17°	702.5
18°	676.8
19°	654.2
20°	634.1
21°	614.8
22°	592.8
23°	567.6
24°	538.0
25°	501.6
26°	462.2
27°	418.3
28°	374.5
29°	327.3
30°	275.4
31°	226.7
32°	181.9
32.5°	162.4
33°	142.7
34°	109.4
35°	80.9
36°	59.3
37°	44.1
37.5°	38.2
38°	33.1
39°	25.7
40°	20.3
42.5°	11.5
45°	6.6



TEST NUMBER: P1262004  
CATALOG NUMBER: P3AS05R509727DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	3.7
50°	1.4
52.5°	0.6
55°	0.4
57.5°	0.4
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)