

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262774

Luminaire Tested: P3AS13R459727DE010 E3DLD1LI

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1262774  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R459727DE010 E3DLD1LI  
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 706.0 lumens  
Efficiency: N/A  
Efficacy: 48.4 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262774

CATALOG NUMBER: P3AS13R459727DE010 E3DLD1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1262774

CATALOG NUMBER: P3AS13R459727DE010 E3DLD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  |  | 99  | 97  | 96  |  | 96  |
| 2   | 106 | 100 | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 91  | 88  |  | 92  | 89  | 86  |  | 89  |
| 3   | 99  | 92  | 86  | 82  | 97  | 90  | 85  | 81  | 88  | 83  | 80  |  | 85  | 81  | 78  |  | 83  |
| 4   | 94  | 85  | 78  | 74  | 92  | 84  | 78  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 5   | 88  | 79  | 72  | 67  | 86  | 78  | 71  | 67  | 76  | 70  | 66  |  | 74  | 69  | 65  |  | 72  |
| 6   | 83  | 73  | 66  | 61  | 81  | 72  | 66  | 61  | 71  | 65  | 61  |  | 69  | 64  | 60  |  | 68  |
| 7   | 78  | 68  | 61  | 57  | 77  | 67  | 61  | 56  | 66  | 60  | 56  |  | 65  | 60  | 56  |  | 64  |
| 8   | 74  | 64  | 57  | 52  | 73  | 63  | 57  | 52  | 62  | 56  | 52  |  | 61  | 56  | 52  |  | 60  |
| 9   | 70  | 60  | 53  | 49  | 69  | 59  | 53  | 49  | 58  | 52  | 48  |  | 57  | 52  | 48  |  | 56  |
| 10  | 67  | 56  | 50  | 45  | 66  | 56  | 49  | 45  | 55  | 49  | 45  |  | 54  | 49  | 45  |  | 53  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 149681 |
| 5°  | 147039 |
| 10° | 139142 |
| 15° | 126902 |
| 20° | 112220 |
| 25° | 97433  |
| 30° | 83633  |
| 35° | 69707  |
| 40° | 51926  |
| 45° | 31786  |
| 50° | 14703  |
| 55° | 11507  |
| 60° | 11052  |
| 65° | 10118  |
| 70° | 9361   |
| 75° | 8981   |
| 80° | 8208   |
| 85° | 6038   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31786 cd/sqm

TEST NUMBER: P1262774

CATALOG NUMBER: P3AS13R459727DE010 E3DLD1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 62.4   | 8.8       |
| 10°-20°   | 155.6  | 22.0      |
| 20°-30°   | 184.9  | 26.2      |
| 30°-40°   | 160.7  | 22.8      |
| 40°-50°   | 80.6   | 11.4      |
| 50°-60°   | 28.0   | 4.0       |
| 60°-70°   | 19.6   | 2.8       |
| 70°-80°   | 10.9   | 1.5       |
| 80°-90°   | 3.3    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 402.9  | 57.1      |
| 0°-40°    | 563.6  | 79.8      |
| 0°-60°    | 672.1  | 95.2      |
| 0°-90°    | 706.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 706.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 683 |      |
| 5°  | 668 | 62   |
| 15° | 559 | 156  |
| 25° | 403 | 185  |
| 35° | 260 | 161  |
| 45° | 102 | 81   |
| 55° | 30  | 28   |
| 65° | 20  | 20   |
| 75° | 11  | 11   |
| 85° | 2   | 3    |
| 90° | 0   |      |

TEST NUMBER: P1262774

CATALOG NUMBER: P3AS13R459727DE010 E3DLD1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 682.6 |
| 2.5°  | 679.4 |
| 5°    | 668.0 |
| 7.5°  | 650.1 |
| 10°   | 624.9 |
| 12.5° | 593.9 |
| 15°   | 559.0 |
| 17.5° | 519.9 |
| 20°   | 480.9 |
| 22.5° | 441.0 |
| 25°   | 402.7 |
| 27.5° | 366.1 |
| 30°   | 330.3 |
| 32.5° | 296.2 |
| 35°   | 260.4 |
| 37.5° | 222.1 |
| 40°   | 181.4 |
| 42.5° | 141.6 |
| 45°   | 102.5 |
| 47.5° | 67.5  |
| 50°   | 43.1  |
| 52.5° | 33.4  |
| 55°   | 30.1  |
| 57.5° | 27.7  |
| 60°   | 25.2  |
| 62.5° | 22.8  |
| 65°   | 19.5  |
| 67.5° | 17.1  |
| 70°   | 14.6  |
| 72.5° | 12.2  |
| 75°   | 10.6  |
| 77.5° | 8.1   |
| 80°   | 6.5   |
| 82.5° | 4.9   |
| 85°   | 2.4   |
| 87.5° | 1.6   |
| 90°   | 0.0   |

(END OF REPORT)