

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262006

Luminaire Tested: P3AS05R509727DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509727DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 231.0 lumens
Efficiency: N/A
Efficacy: 32.1 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262006

CATALOG NUMBER: P3AS05R509727DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1262006

CATALOG NUMBER: P3AS05R509727DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	76	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73547
5°	72067
10°	67512
15°	60432
20°	50848
25°	38809
30°	25219
35°	14964
40°	8645
45°	4342
50°	1603
55°	1262
60°	1184
65°	1090
70°	1026
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4342 cd/sqm

TEST NUMBER: P1262006

CATALOG NUMBER: P3AS05R509727DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.5	13.2
10°-20°	73.6	31.9
20°-30°	72.2	31.3
30°-40°	36.4	15.8
40°-50°	11.5	5.0
50°-60°	3.0	1.3
60°-70°	2.1	0.9
70°-80°	1.3	0.5
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	176.3	76.3
0°-40°	212.7	92.1
0°-60°	227.2	98.3
0°-90°	231.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	231.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	335	
5°	327	30
15°	266	74
25°	160	72
35°	56	36
45°	14	12
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1262006

CATALOG NUMBER: P3AS05R509727DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	335.4
2.5°	333.3
5°	327.4
7.5°	316.7
10°	303.2
12.5°	285.7
15°	266.2
17.5°	243.6
20°	217.9
22.5°	190.2
25°	160.4
27.5°	128.8
30°	99.6
32.5°	75.0
35°	55.9
37.5°	41.3
40°	30.2
42.5°	21.4
45°	14.0
47.5°	8.0
50°	4.7
52.5°	3.5
55°	3.3
57.5°	2.9
60°	2.7
62.5°	2.5
65°	2.1
67.5°	1.8
70°	1.6
72.5°	1.4
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)