

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262010

Luminaire Tested: P3AS05R509727DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262010
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509727DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 309.0 lumens
Efficiency: N/A
Efficacy: 42.9 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262010
CATALOG NUMBER: P3AS05R509727DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1262010
 CATALOG NUMBER: P3AS05R509727DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73			
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68			
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60			
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56			
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89861
5°	87453
10°	80649
15°	70920
20°	59342
25°	47059
30°	34512
35°	23744
40°	15085
45°	8435
50°	4571
55°	3823
60°	3289
65°	3061
70°	2693
75°	2457
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8435 cd/sqm



TEST NUMBER: P1262010
 CATALOG NUMBER: P3AS05R509727DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.8	11.9
10°-20°	86.5	28.0
20°-30°	88.5	28.6
30°-40°	56.1	18.2
40°-50°	22.3	7.2
50°-60°	9.0	2.9
60°-70°	5.8	1.9
70°-80°	3.0	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	211.8	68.6
0°-40°	267.9	86.7
0°-60°	299.3	96.9
0°-90°	309.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	309.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	410	
5°	397	37
15°	312	87
25°	194	89
35°	89	56
45°	27	22
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1262010
CATALOG NUMBER: P3AS05R509727DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	409.8
2.5°	406.9
5°	397.3
7.5°	382.2
10°	362.2
12.5°	338.3
15°	312.4
17.5°	284.0
20°	254.3
22.5°	224.6
25°	194.5
27.5°	164.4
30°	136.3
32.5°	111.2
35°	88.7
37.5°	69.4
40°	52.7
42.5°	38.9
45°	27.2
47.5°	18.4
50°	13.4
52.5°	11.3
55°	10.0
57.5°	8.8
60°	7.5
62.5°	6.7
65°	5.9
67.5°	5.0
70°	4.2
72.5°	3.3
75°	2.9
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)