

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262052

Luminaire Tested: P3AS05R559727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 305.0 lumens
Efficiency: N/A
Efficacy: 42.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262052
CATALOG NUMBER: P3AS05R559727DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1262052
 CATALOG NUMBER: P3AS05R559727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92				92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79				79
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55				55
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52				52
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49				49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82976
5°	80893
10°	75193
15°	66970
20°	56915
25°	45922
30°	35018
35°	24895
40°	16431
45°	9737
50°	5731
55°	3517
60°	3114
65°	2802
70°	2436
75°	2118
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9737 cd/sqm



TEST NUMBER: P1262052
 CATALOG NUMBER: P3AS05R559727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.1	11.2
10°-20°	81.8	26.8
20°-30°	86.6	28.4
30°-40°	58.5	19.2
40°-50°	25.7	8.4
50°-60°	9.2	3.0
60°-70°	5.4	1.8
70°-80°	2.8	0.9
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	202.5	66.4
0°-40°	261.0	85.6
0°-60°	295.9	97.0
0°-90°	305.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	305.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	378	
5°	368	34
15°	295	82
25°	190	87
35°	93	59
45°	31	26
55°	9	9
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1262052
CATALOG NUMBER: P3AS05R559727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	378.4
2.5°	375.4
5°	367.5
7.5°	354.5
10°	337.7
12.5°	317.6
15°	295.0
17.5°	269.8
20°	243.9
22.5°	216.6
25°	189.8
27.5°	163.4
30°	138.3
32.5°	114.4
35°	93.0
37.5°	73.7
40°	57.4
42.5°	43.2
45°	31.4
47.5°	23.0
50°	16.8
52.5°	11.7
55°	9.2
57.5°	8.4
60°	7.1
62.5°	6.3
65°	5.4
67.5°	4.6
70°	3.8
72.5°	3.4
75°	2.5
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)