

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262059

Luminaire Tested: P3AS05R609727DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262059
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609727DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 502.0 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262059
CATALOG NUMBER: P3AS05R609727DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1262059

CATALOG NUMBER: P3AS05R609727DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67	67	67	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131525
5°	124169
10°	120951
15°	118185
20°	109886
25°	98231
30°	75024
35°	43313
40°	16803
45°	7008
50°	1535
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7008 cd/sqm



TEST NUMBER: P1262059
 CATALOG NUMBER: P3AS05R609727DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.3	10.6
10°-20°	145.0	28.9
20°-30°	181.6	36.2
30°-40°	101.5	20.2
40°-50°	19.3	3.8
50°-60°	1.0	0.2
60°-70°	0.2	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.9	75.7
0°-40°	481.4	95.9
0°-60°	501.7	99.9
0°-90°	502.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	502.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	600	
5°	564	53
15°	521	145
25°	406	182
35°	162	102
45°	23	19
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1262059
CATALOG NUMBER: P3AS05R609727DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	599.8
1°	597.4
2°	589.6
3°	580.3
4°	571.7
5°	564.1
6°	558.3
7°	553.4
8°	549.7
9°	546.2
10°	543.2
11°	540.1
12°	536.6
13°	532.3
14°	527.1
15°	520.6
16°	512.6
17°	503.5
18°	493.3
19°	481.5
20°	470.9
21°	459.4
22°	447.5
23°	434.9
24°	421.2
25°	406.0
26°	388.1
27°	368.2
28°	345.8
29°	322.0
30°	296.3
31°	270.4
32°	243.8
32.5°	229.2
33°	216.0
34°	188.7
35°	161.8
36°	137.6
37°	111.9
37.5°	100.2
38°	88.7
39°	71.5
40°	58.7
42.5°	35.7
45°	22.6



TEST NUMBER: P1262059
CATALOG NUMBER: P3AS05R609727DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	12.5
50°	4.5
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)