

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262064

Luminaire Tested: P3AS05R609727DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1262064  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R609727DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 97CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 216.0 lumens  
Efficiency: N/A  
Efficacy: 30.0 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262064

CATALOG NUMBER: P3AS05R609727DE010 E3DL1GPH

### Luminous Intensity Polar Plot



TEST NUMBER: P1262064

CATALOG NUMBER: P3AS05R609727DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 96  | 94  | 93  |    |    |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  | 94  | 91  | 89  | 91  | 89  | 87  | 85  |    |    |
| 3   | 101 | 95  | 89  | 85  | 99  | 93  | 88  | 84  | 91  | 86  | 83  | 88  | 85  | 82  | 86  | 83  | 81  | 79  |    |    |
| 4   | 96  | 88  | 82  | 78  | 94  | 87  | 81  | 77  | 85  | 80  | 76  | 83  | 79  | 75  | 81  | 77  | 75  | 73  |    |    |
| 5   | 91  | 82  | 76  | 71  | 89  | 81  | 75  | 71  | 79  | 74  | 70  | 78  | 73  | 70  | 76  | 72  | 69  | 68  |    |    |
| 6   | 86  | 77  | 70  | 66  | 84  | 76  | 70  | 66  | 74  | 69  | 65  | 73  | 68  | 65  | 72  | 68  | 64  | 63  |    |    |
| 7   | 82  | 72  | 66  | 61  | 80  | 71  | 65  | 61  | 70  | 65  | 61  | 69  | 64  | 60  | 68  | 63  | 60  | 59  |    |    |
| 8   | 77  | 68  | 61  | 57  | 76  | 67  | 61  | 57  | 66  | 60  | 57  | 65  | 60  | 56  | 64  | 59  | 56  | 55  |    |    |
| 9   | 74  | 64  | 57  | 53  | 72  | 63  | 57  | 53  | 62  | 57  | 53  | 61  | 56  | 53  | 60  | 56  | 53  | 51  |    |    |
| 10  | 70  | 60  | 54  | 50  | 69  | 60  | 54  | 50  | 59  | 53  | 50  | 58  | 53  | 50  | 57  | 53  | 49  | 48  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 51005 |
| 5°  | 50517 |
| 10° | 49053 |
| 15° | 45948 |
| 20° | 40674 |
| 25° | 34018 |
| 30° | 26662 |
| 35° | 19354 |
| 40° | 12881 |
| 45° | 8032  |
| 50° | 4332  |
| 55° | 1262  |
| 60° | 1184  |
| 65° | 1090  |
| 70° | 1026  |
| 75° | 1017  |
| 80° | 1010  |
| 85° | 1006  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 8032 cd/sqm

TEST NUMBER: P1262064

CATALOG NUMBER: P3AS05R609727DE010 E3DL1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 21.6   | 10.0      |
| 10°-20°   | 56.2   | 26.0      |
| 20°-30°   | 64.0   | 29.6      |
| 30°-40°   | 45.4   | 21.0      |
| 40°-50°   | 20.6   | 9.5       |
| 50°-60°   | 4.4    | 2.0       |
| 60°-70°   | 2.1    | 1.0       |
| 70°-80°   | 1.3    | 0.6       |
| 80°-90°   | 0.4    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 141.8  | 65.6      |
| 0°-40°    | 187.2  | 86.7      |
| 0°-60°    | 212.2  | 98.2      |
| 0°-90°    | 216.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 216.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 233 |      |
| 5°  | 230 | 22   |
| 15° | 202 | 56   |
| 25° | 141 | 64   |
| 35° | 72  | 45   |
| 45° | 26  | 21   |
| 55° | 3   | 4    |
| 65° | 2   | 2    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1262064

CATALOG NUMBER: P3AS05R609727DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 232.6 |
| 2.5°  | 231.8 |
| 5°    | 229.5 |
| 7.5°  | 225.6 |
| 10°   | 220.3 |
| 12.5° | 212.7 |
| 15°   | 202.4 |
| 17.5° | 189.5 |
| 20°   | 174.3 |
| 22.5° | 157.9 |
| 25°   | 140.6 |
| 27.5° | 123.0 |
| 30°   | 105.3 |
| 32.5° | 88.5  |
| 35°   | 72.3  |
| 37.5° | 57.9  |
| 40°   | 45.0  |
| 42.5° | 34.1  |
| 45°   | 25.9  |
| 47.5° | 19.3  |
| 50°   | 12.7  |
| 52.5° | 6.0   |
| 55°   | 3.3   |
| 57.5° | 2.9   |
| 60°   | 2.7   |
| 62.5° | 2.5   |
| 65°   | 2.1   |
| 67.5° | 1.8   |
| 70°   | 1.6   |
| 72.5° | 1.4   |
| 75°   | 1.2   |
| 77.5° | 1.0   |
| 80°   | 0.8   |
| 82.5° | 0.6   |
| 85°   | 0.4   |
| 87.5° | 0.2   |
| 90°   | 0.0   |

(END OF REPORT)