

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262850

Luminaire Tested: P3AS13R609727DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609727DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 97CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1051.9 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262850
CATALOG NUMBER: P3AS13R609727DE010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1262850
 CATALOG NUMBER: P3AS13R609727DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81				81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76				76
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71				71
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	70	68	66				66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62				62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58				58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55				55
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	251208
5°	241250
10°	248381
15°	251579
20°	222153
25°	187220
30°	151846
35°	98886
40°	45428
45°	17397
50°	5833
55°	1567
60°	1447
65°	1245
70°	1026
75°	1356
80°	1010
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17397 cd/sqm



TEST NUMBER: P1262850
 CATALOG NUMBER: P3AS13R609727DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.5	10.0
10°-20°	303.5	28.8
20°-30°	354.0	33.6
30°-40°	228.4	21.7
40°-50°	51.2	4.9
50°-60°	5.1	0.5
60°-70°	2.4	0.2
70°-80°	1.4	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	762.9	72.5
0°-40°	991.3	94.2
0°-60°	1047.6	99.6
0°-90°	1051.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1051.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1146	
5°	1096	105
15°	1108	303
25°	774	354
35°	369	228
45°	56	51
55°	4	5
65°	2	2
75°	2	1
85°	1	1
90°	0	



TEST NUMBER: P1262850
CATALOG NUMBER: P3AS13R609727DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1145.6
2.5°	1126.9
5°	1096.0
7.5°	1094.4
10°	1115.5
12.5°	1129.3
15°	1108.2
17.5°	1044.7
20°	952.0
22.5°	855.1
25°	773.8
27.5°	694.0
30°	599.7
32.5°	489.0
35°	369.4
37.5°	252.2
40°	158.7
42.5°	95.2
45°	56.1
47.5°	32.5
50°	17.1
52.5°	5.7
55°	4.1
57.5°	3.3
60°	3.3
62.5°	2.4
65°	2.4
67.5°	2.4
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)