

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262852

Luminaire Tested: P3AS13R609727DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262852
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609727DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 975.0 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262852
CATALOG NUMBER: P3AS13R609727DE010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1262852
 CATALOG NUMBER: P3AS13R609727DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82				82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77				77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	71	69	67				67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63				63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59				59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53				53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	255462
5°	241162
10°	234888
15°	229536
20°	213402
25°	190777
30°	145719
35°	84136
40°	32661
45°	13614
50°	3002
55°	459
60°	351
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13614 cd/sqm



TEST NUMBER: P1262852
 CATALOG NUMBER: P3AS13R609727DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.4	10.6
10°-20°	281.6	28.9
20°-30°	352.7	36.2
30°-40°	197.2	20.2
40°-50°	37.5	3.8
50°-60°	1.9	0.2
60°-70°	0.4	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.8	75.7
0°-40°	935.0	95.9
0°-60°	974.4	99.9
0°-90°	975.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	975.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1165	
5°	1096	103
15°	1011	282
25°	788	353
35°	314	197
45°	44	37
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1262852
CATALOG NUMBER: P3AS13R609727DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1165.0
1°	1160.2
2°	1145.1
3°	1127.1
4°	1110.4
5°	1095.6
6°	1084.4
7°	1074.9
8°	1067.7
9°	1060.9
10°	1054.9
11°	1048.9
12°	1042.2
13°	1033.8
14°	1023.8
15°	1011.1
16°	995.5
17°	978.0
18°	958.0
19°	935.3
20°	914.5
21°	892.2
22°	869.1
23°	844.7
24°	818.0
25°	788.5
26°	753.8
27°	715.1
28°	671.6
29°	625.4
30°	575.5
31°	525.3
32°	473.4
32.5°	445.1
33°	419.6
34°	366.5
35°	314.3
36°	267.2
37°	217.4
37.5°	194.6
38°	172.3
39°	138.8
40°	114.1
42.5°	69.4
45°	43.9

TEST NUMBER: P1262852
CATALOG NUMBER: P3AS13R609727DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	24.3
50°	8.8
52.5°	2.0
55°	1.2
57.5°	0.8
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)