

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262081

Luminaire Tested: P3AS05R609727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262081
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 305.0 lumens
Efficiency: N/A
Efficacy: 42.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262081
CATALOG NUMBER: P3AS05R609727DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1262081
 CATALOG NUMBER: P3AS05R609727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77296
5°	75567
10°	70740
15°	63474
20°	54581
25°	45124
30°	35651
35°	26475
40°	18234
45°	11443
50°	6277
55°	3670
60°	3289
65°	2802
70°	2436
75°	2457
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11443 cd/sqm



TEST NUMBER: P1262081
 CATALOG NUMBER: P3AS05R609727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.0	10.5
10°-20°	77.6	25.5
20°-30°	85.2	27.9
30°-40°	62.1	20.3
40°-50°	29.3	9.6
50°-60°	9.6	3.1
60°-70°	5.4	1.8
70°-80°	2.9	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	194.8	63.9
0°-40°	256.8	84.2
0°-60°	295.7	97.0
0°-90°	305.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	305.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	352	
5°	343	32
15°	280	78
25°	186	85
35°	99	62
45°	37	29
55°	10	10
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1262081
CATALOG NUMBER: P3AS05R609727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	352.5
2.5°	350.4
5°	343.3
7.5°	332.4
10°	317.7
12.5°	300.1
15°	279.6
17.5°	257.4
20°	233.9
22.5°	210.0
25°	186.5
27.5°	163.0
30°	140.8
32.5°	119.5
35°	98.9
37.5°	80.5
40°	63.7
42.5°	49.0
45°	36.9
47.5°	26.8
50°	18.4
52.5°	12.2
55°	9.6
57.5°	8.4
60°	7.5
62.5°	6.3
65°	5.4
67.5°	4.6
70°	3.8
72.5°	3.4
75°	2.9
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)