

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262857

Luminaire Tested: P3AS13R609727DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262857
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609727DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 97CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 592.0 lumens
Efficiency: N/A
Efficacy: 40.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262857
CATALOG NUMBER: P3AS13R609727DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1262857
 CATALOG NUMBER: P3AS13R609727DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | | | |
| 2 | 107 | 101 | 97 | 93 | 104 | 100 | 96 | 92 | 96 | 93 | 90 | 93 | 91 | 88 | 91 | 88 | 86 | 85 | | | |
| 3 | 101 | 94 | 88 | 84 | 99 | 92 | 87 | 83 | 90 | 86 | 82 | 87 | 84 | 81 | 85 | 82 | 80 | 78 | | | |
| 4 | 95 | 87 | 81 | 77 | 93 | 86 | 80 | 76 | 84 | 79 | 75 | 82 | 78 | 74 | 80 | 76 | 73 | 72 | | | |
| 5 | 90 | 81 | 75 | 70 | 88 | 80 | 74 | 70 | 78 | 73 | 69 | 77 | 72 | 69 | 75 | 71 | 68 | 66 | | | |
| 6 | 85 | 76 | 69 | 65 | 84 | 75 | 69 | 65 | 73 | 68 | 64 | 72 | 67 | 64 | 71 | 66 | 63 | 62 | | | |
| 7 | 81 | 71 | 65 | 60 | 79 | 70 | 64 | 60 | 69 | 64 | 60 | 68 | 63 | 59 | 67 | 62 | 59 | 58 | | | |
| 8 | 77 | 67 | 60 | 56 | 75 | 66 | 60 | 56 | 65 | 60 | 56 | 64 | 59 | 55 | 63 | 58 | 55 | 54 | | | |
| 9 | 73 | 63 | 57 | 52 | 72 | 62 | 56 | 52 | 61 | 56 | 52 | 60 | 55 | 52 | 60 | 55 | 52 | 50 | | | |
| 10 | 69 | 59 | 53 | 49 | 68 | 59 | 53 | 49 | 58 | 53 | 49 | 57 | 52 | 49 | 56 | 52 | 49 | 47 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 150032 |
| 5° | 146665 |
| 10° | 137317 |
| 15° | 123179 |
| 20° | 105943 |
| 25° | 87586 |
| 30° | 69226 |
| 35° | 51397 |
| 40° | 35409 |
| 45° | 22204 |
| 50° | 12213 |
| 55° | 7149 |
| 60° | 6403 |
| 65° | 5500 |
| 70° | 4680 |
| 75° | 4829 |
| 80° | 4167 |
| 85° | 4026 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22204 cd/sqm



TEST NUMBER: P1262857
 CATALOG NUMBER: P3AS13R609727DE010 E3DL1WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 62.0 | 10.5 |
| 10°-20° | 150.7 | 25.5 |
| 20°-30° | 165.3 | 27.9 |
| 30°-40° | 120.4 | 20.3 |
| 40°-50° | 56.9 | 9.6 |
| 50°-60° | 18.6 | 3.1 |
| 60°-70° | 10.5 | 1.8 |
| 70°-80° | 5.7 | 1.0 |
| 80°-90° | 1.8 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 378.0 | 63.9 |
| 0°-40° | 498.5 | 84.2 |
| 0°-60° | 574.0 | 97.0 |
| 0°-90° | 592.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 592.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 684 | |
| 5° | 666 | 62 |
| 15° | 543 | 151 |
| 25° | 362 | 165 |
| 35° | 192 | 120 |
| 45° | 72 | 57 |
| 55° | 19 | 19 |
| 65° | 11 | 11 |
| 75° | 6 | 6 |
| 85° | 2 | 2 |
| 90° | 0 | |

TEST NUMBER: P1262857

CATALOG NUMBER: P3AS13R609727DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 684.2 |
| 2.5° | 680.1 |
| 5° | 666.3 |
| 7.5° | 645.1 |
| 10° | 616.7 |
| 12.5° | 582.5 |
| 15° | 542.6 |
| 17.5° | 499.5 |
| 20° | 454.0 |
| 22.5° | 407.6 |
| 25° | 362.0 |
| 27.5° | 316.5 |
| 30° | 273.4 |
| 32.5° | 231.9 |
| 35° | 192.0 |
| 37.5° | 156.2 |
| 40° | 123.7 |
| 42.5° | 95.2 |
| 45° | 71.6 |
| 47.5° | 52.1 |
| 50° | 35.8 |
| 52.5° | 23.6 |
| 55° | 18.7 |
| 57.5° | 16.3 |
| 60° | 14.6 |
| 62.5° | 12.2 |
| 65° | 10.6 |
| 67.5° | 8.9 |
| 70° | 7.3 |
| 72.5° | 6.5 |
| 75° | 5.7 |
| 77.5° | 4.1 |
| 80° | 3.3 |
| 82.5° | 2.4 |
| 85° | 1.6 |
| 87.5° | 0.8 |
| 90° | 0.0 |

(END OF REPORT)