

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262112

Luminaire Tested: P3AS05R709727DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262112
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709727DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 524.0 lumens
Efficiency: N/A
Efficacy: 72.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262112

CATALOG NUMBER: P3AS05R709727DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1262112

CATALOG NUMBER: P3AS05R709727DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104049
5°	99295
10°	94476
15°	91942
20°	88534
25°	83811
30°	77936
35°	65478
40°	42193
45°	19599
50°	5151
55°	1300
60°	1272
65°	1090
70°	1090
75°	1101
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19599 cd/sqm

TEST NUMBER: P1262112

CATALOG NUMBER: P3AS05R709727DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.2	8.1
10°-20°	113.8	21.7
20°-30°	159.0	30.3
30°-40°	147.4	28.1
40°-50°	52.8	10.1
50°-60°	4.5	0.9
60°-70°	2.2	0.4
70°-80°	1.5	0.3
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	315.0	60.1
0°-40°	462.4	88.3
0°-60°	519.8	99.2
0°-90°	524.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	524.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	474	
5°	451	42
15°	405	114
25°	346	159
35°	245	147
45°	63	53
55°	3	4
65°	2	2
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P1262112

CATALOG NUMBER: P3AS05R709727DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	474.5
2.5°	467.4
5°	451.1
7.5°	436.0
10°	424.3
12.5°	414.6
15°	405.0
17.5°	393.3
20°	379.4
22.5°	363.5
25°	346.4
27.5°	328.8
30°	307.8
32.5°	281.0
35°	244.6
37.5°	198.1
40°	147.4
42.5°	100.5
45°	63.2
47.5°	35.2
50°	15.1
52.5°	5.0
55°	3.4
57.5°	2.9
60°	2.9
62.5°	2.5
65°	2.1
67.5°	2.1
70°	1.7
72.5°	1.7
75°	1.3
77.5°	1.3
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)