

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262869

Luminaire Tested: P3AS13R609727DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262869
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609727DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 856.0 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262869

CATALOG NUMBER: P3AS13R609727DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1262869

CATALOG NUMBER: P3AS13R609727DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202133
5°	200220
10°	194385
15°	182112
20°	161177
25°	134838
30°	105687
35°	76667
40°	51010
45°	31786
50°	17193
55°	4970
60°	4649
65°	4203
70°	4167
75°	4151
80°	4167
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31786 cd/sqm

TEST NUMBER: P1262869

CATALOG NUMBER: P3AS13R609727DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.7	10.0
10°-20°	222.6	26.0
20°-30°	253.7	29.6
30°-40°	179.9	21.0
40°-50°	81.6	9.5
50°-60°	17.3	2.0
60°-70°	8.3	1.0
70°-80°	5.2	0.6
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	561.9	65.6
0°-40°	741.8	86.7
0°-60°	840.7	98.2
0°-90°	856.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	856.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	922	
5°	910	86
15°	802	223
25°	557	254
35°	286	180
45°	102	82
55°	13	17
65°	8	8
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1262869

CATALOG NUMBER: P3AS13R609727DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	921.8
2.5°	918.5
5°	909.6
7.5°	894.1
10°	873.0
12.5°	842.9
15°	802.2
17.5°	750.9
20°	690.7
22.5°	625.6
25°	557.3
27.5°	487.3
30°	417.4
32.5°	350.7
35°	286.4
37.5°	229.4
40°	178.2
42.5°	135.1
45°	102.5
47.5°	76.5
50°	50.4
52.5°	23.6
55°	13.0
57.5°	11.4
60°	10.6
62.5°	9.8
65°	8.1
67.5°	7.3
70°	6.5
72.5°	5.7
75°	4.9
77.5°	4.1
80°	3.3
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)