

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262165

Luminaire Tested: P3AS09R109727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262165
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R109727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R10 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 297.0 lumens
Efficiency: N/A
Efficacy: 23.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262165

CATALOG NUMBER: P3AS09R109727DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1262165

CATALOG NUMBER: P3AS09R109727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128082
5°	118380
10°	94498
15°	71397
20°	54348
25°	41422
30°	29675
35°	19354
40°	11879
45°	7195
50°	4776
55°	3670
60°	3158
65°	2750
70°	2500
75°	2457
80°	1768
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7195 cd/sqm

TEST NUMBER: P1262165

CATALOG NUMBER: P3AS09R109727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.6	16.0
10°-20°	87.9	29.6
20°-30°	78.2	26.3
30°-40°	46.3	15.6
40°-50°	19.0	6.4
50°-60°	8.9	3.0
60°-70°	5.4	1.8
70°-80°	2.9	1.0
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	213.8	72.0
0°-40°	260.1	87.6
0°-60°	288.0	97.0
0°-90°	297.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	297.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	584	
5°	538	48
15°	314	88
25°	171	78
35°	72	46
45°	23	19
55°	10	9
65°	5	5
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1262165

CATALOG NUMBER: P3AS09R109727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	584.1
1°	582.6
2°	578.3
3°	569.6
4°	555.1
5°	537.8
6°	518.9
7°	496.8
8°	473.6
9°	450.0
10°	424.4
12.5°	366.1
15°	314.5
17.5°	270.1
20°	232.9
22.5°	200.2
25°	171.2
27.5°	143.2
30°	117.2
32.5°	93.6
35°	72.3
37.5°	55.5
40°	41.5
42.5°	30.9
45°	23.2
47.5°	17.8
50°	14.0
52.5°	11.6
55°	9.6
57.5°	8.2
60°	7.2
62.5°	6.3
65°	5.3
67.5°	4.8
70°	3.9
72.5°	3.4
75°	2.9
77.5°	1.9
80°	1.4
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)