

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262872

Luminaire Tested: P3AS13R659727DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262872
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659727DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1006.0 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262872

CATALOG NUMBER: P3AS13R659727DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1262872

CATALOG NUMBER: P3AS13R659727DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		60	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	245836
5°	231388
10°	228430
15°	224405
20°	211885
25°	196657
30°	152859
35°	88419
40°	35638
45°	16405
50°	6379
55°	2485
60°	2149
65°	2127
70°	2116
75°	2033
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16405 cd/sqm

TEST NUMBER: P1262872

CATALOG NUMBER: P3AS13R659727DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	9.9
10°-20°	276.0	27.4
20°-30°	361.4	35.9
30°-40°	209.3	20.8
40°-50°	44.8	4.5
50°-60°	7.3	0.7
60°-70°	4.1	0.4
70°-80°	2.3	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.3	73.3
0°-40°	946.6	94.1
0°-60°	998.7	99.3
0°-90°	1006.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1006.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1121	
5°	1051	100
15°	988	276
25°	813	361
35°	330	209
45°	53	45
55°	6	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1262872

CATALOG NUMBER: P3AS13R659727DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1121.1
2.5°	1089.4
5°	1051.2
7.5°	1035.7
10°	1025.9
12.5°	1012.1
15°	988.5
17.5°	951.9
20°	908.0
22.5°	866.5
25°	812.8
27.5°	722.5
30°	603.7
32.5°	467.8
35°	330.3
37.5°	209.1
40°	124.5
42.5°	78.1
45°	52.9
47.5°	34.2
50°	18.7
52.5°	8.9
55°	6.5
57.5°	5.7
60°	4.9
62.5°	4.9
65°	4.1
67.5°	3.3
70°	3.3
72.5°	2.4
75°	2.4
77.5°	1.6
80°	1.6
82.5°	0.8
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)