

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262183

Luminaire Tested: P3AS09R159727DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262183
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159727DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 636.0 lumens
Efficiency: N/A
Efficacy: 57.3 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262183

CATALOG NUMBER: P3AS09R159727DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1262183

CATALOG NUMBER: P3AS09R159727DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	543312
5°	482279
10°	334908
15°	198072
20°	112803
25°	64480
30°	35676
35°	19033
40°	10534
45°	5706
50°	3548
55°	2829
60°	2412
65°	2231
70°	1988
75°	2118
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5706 cd/sqm

TEST NUMBER: P1262183

CATALOG NUMBER: P3AS09R159727DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.3	29.3
10°-20°	245.9	38.7
20°-30°	126.6	19.9
30°-40°	47.6	7.5
40°-50°	15.6	2.4
50°-60°	6.7	1.1
60°-70°	4.3	0.7
70°-80°	2.5	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	558.8	87.9
0°-40°	606.4	95.3
0°-60°	628.6	98.8
0°-90°	636.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	636.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2478	
5°	2191	186
15°	872	246
25°	266	127
35°	71	48
45°	18	16
55°	7	7
65°	4	4
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1262183

CATALOG NUMBER: P3AS09R159727DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2477.7
1°	2472.8
2°	2440.3
3°	2378.4
4°	2297.0
5°	2191.0
6°	2070.9
7°	1939.1
8°	1792.7
9°	1648.1
10°	1504.1
12.5°	1157.4
15°	872.5
17.5°	653.1
20°	483.4
22.5°	360.9
25°	266.5
27.5°	194.2
30°	140.9
32.5°	99.9
35°	71.1
37.5°	50.9
40°	36.8
42.5°	26.3
45°	18.4
47.5°	13.5
50°	10.4
52.5°	8.6
55°	7.4
57.5°	6.1
60°	5.5
62.5°	4.9
65°	4.3
67.5°	3.7
70°	3.1
72.5°	3.1
75°	2.5
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)