

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262909

Luminaire Tested: P3AS13R709727DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262909
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709727DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 971.0 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262909
CATALOG NUMBER: P3AS13R709727DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1262909
 CATALOG NUMBER: P3AS13R709727DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79		
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61		
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	188801
5°	178032
10°	168801
15°	165767
20°	159777
25°	150614
30°	149542
35°	130232
40°	84244
45°	39818
50°	5595
55°	459
60°	351
65°	415
70°	256
75°	339
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 39818 cd/sqm



TEST NUMBER: P1262909
 CATALOG NUMBER: P3AS13R709727DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.5	7.8
10°-20°	205.1	21.1
20°-30°	290.1	29.9
30°-40°	291.5	30.0
40°-50°	104.8	10.8
50°-60°	2.8	0.3
60°-70°	0.6	0.1
70°-80°	0.4	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	570.7	58.8
0°-40°	862.2	88.8
0°-60°	969.9	99.9
0°-90°	971.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	971.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	861	
5°	809	76
15°	730	205
25°	622	290
35°	486	292
45°	128	105
55°	1	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1262909
CATALOG NUMBER: P3AS13R709727DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	861.0
1°	858.6
2°	851.0
3°	839.1
4°	823.9
5°	808.8
6°	794.4
7°	783.3
8°	773.3
9°	765.3
10°	758.1
11°	752.1
12°	746.6
13°	741.0
14°	735.8
15°	730.2
16°	723.4
17°	716.3
18°	707.5
19°	696.7
20°	684.7
21°	671.6
22°	658.4
23°	645.7
24°	633.3
25°	622.5
26°	615.0
27°	609.0
28°	604.2
29°	598.6
30°	590.6
31°	579.1
32°	562.7
32.5°	553.5
33°	541.2
34°	516.8
35°	486.5
36°	453.0
37°	415.2
37.5°	397.6
38°	373.7
39°	331.0
40°	294.3
42.5°	203.8
45°	128.4



TEST NUMBER: P1262909
CATALOG NUMBER: P3AS13R709727DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	69.0
50°	16.4
52.5°	2.0
55°	1.2
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)