

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262948

Luminaire Tested: P3AS17R159727DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159727DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 325.0 lumens
Efficiency: N/A
Efficacy: 15.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262948

CATALOG NUMBER: P3AS17R159727DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1262948

CATALOG NUMBER: P3AS17R159727DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		100	99	98		97	96	95
2	108	103	98	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	93	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72
6	88	79	73	69		87	79	73	69		77	72	69		76	71	68		74	71	68
7	84	75	69	65		83	74	69	65		73	68	64		72	67	64		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		67	63	60
9	77	68	62	58		76	67	62	58		66	61	58		65	61	57		64	60	57
10	74	64	59	55		73	64	59	55		63	58	55		62	58	55		62	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140142
5°	129540
10°	103405
15°	78116
20°	59482
25°	45341
30°	32461
35°	21201
40°	12996
45°	7846
50°	5219
55°	4052
60°	3465
65°	3009
70°	2693
75°	2711
80°	2020
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7846 cd/sqm

TEST NUMBER: P1262948

CATALOG NUMBER: P3AS17R159727DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	16.0
10°-20°	96.2	29.6
20°-30°	85.6	26.3
30°-40°	50.7	15.6
40°-50°	20.8	6.4
50°-60°	9.8	3.0
60°-70°	5.9	1.8
70°-80°	3.1	1.0
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	233.9	72.0
0°-40°	284.6	87.6
0°-60°	315.2	97.0
0°-90°	325.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	325.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	639	
5°	588	52
15°	344	96
25°	187	86
35°	79	51
45°	25	21
55°	11	10
65°	6	6
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1262948

CATALOG NUMBER: P3AS17R159727DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	639.1
1°	637.5
2°	632.8
3°	623.3
4°	607.5
5°	588.5
6°	567.9
7°	543.6
8°	518.3
9°	492.4
10°	464.4
12.5°	400.6
15°	344.1
17.5°	295.5
20°	254.9
22.5°	219.0
25°	187.4
27.5°	156.7
30°	128.2
32.5°	102.4
35°	79.2
37.5°	60.7
40°	45.4
42.5°	33.8
45°	25.3
47.5°	19.5
50°	15.3
52.5°	12.7
55°	10.6
57.5°	9.0
60°	7.9
62.5°	6.9
65°	5.8
67.5°	5.3
70°	4.2
72.5°	3.7
75°	3.2
77.5°	2.1
80°	1.6
82.5°	1.1
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)