

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262951

Luminaire Tested: P3AS17R159727DE010 E3DLP1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262951  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R159727DE010 E3DLP1MW  
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 664.0 lumens  
Efficiency: N/A  
Efficacy: 31.3 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262951  
CATALOG NUMBER: P3AS17R159727DE010 E3DLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1262951  
 CATALOG NUMBER: P3AS17R159727DE010 E3DLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	286337
5°	264648
10°	211285
15°	159592
20°	121531
25°	92618
30°	66339
35°	43286
40°	26535
45°	16064
50°	10678
55°	8258
60°	7105
65°	6174
70°	5514
75°	5507
80°	4041
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16064 cd/sqm



TEST NUMBER: P1262951  
 CATALOG NUMBER: P3AS17R159727DE010 E3DLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.5	16.0
10°-20°	196.5	29.6
20°-30°	174.9	26.3
30°-40°	103.5	15.6
40°-50°	42.5	6.4
50°-60°	20.0	3.0
60°-70°	12.1	1.8
70°-80°	6.4	1.0
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	477.9	72.0
0°-40°	581.4	87.6
0°-60°	643.9	97.0
0°-90°	664.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	664.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1306	
5°	1202	107
15°	703	196
25°	383	175
35°	162	103
45°	52	42
55°	22	20
65°	12	12
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1262951  
CATALOG NUMBER: P3AS17R159727DE010 E3DLP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1305.8
1°	1302.5
2°	1292.8
3°	1273.4
4°	1241.1
5°	1202.3
6°	1160.2
7°	1110.6
8°	1058.9
9°	1006.0
10°	948.9
12.5°	818.4
15°	703.0
17.5°	603.8
20°	520.8
22.5°	447.5
25°	382.8
27.5°	320.2
30°	262.0
32.5°	209.2
35°	161.7
37.5°	124.0
40°	92.7
42.5°	69.0
45°	51.8
47.5°	39.9
50°	31.3
52.5°	25.9
55°	21.6
57.5°	18.3
60°	16.2
62.5°	14.0
65°	11.9
67.5°	10.8
70°	8.6
72.5°	7.5
75°	6.5
77.5°	4.3
80°	3.2
82.5°	2.2
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)