

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262255

Luminaire Tested: P3AS09R259727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262255
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 393.0 lumens
Efficiency: N/A
Efficacy: 35.4 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262255

CATALOG NUMBER: P3AS09R259727DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1262255

CATALOG NUMBER: P3AS09R259727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142686
5°	136892
10°	119927
15°	96391
20°	74066
25°	56035
30°	40487
35°	26903
40°	16316
45°	9489
50°	6072
55°	4932
60°	4298
65°	3840
70°	3142
75°	3135
80°	2273
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9489 cd/sqm

TEST NUMBER: P1262255

CATALOG NUMBER: P3AS09R259727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.6	14.4
10°-20°	117.4	29.9
20°-30°	106.2	27.0
30°-40°	63.8	16.2
40°-50°	25.3	6.4
50°-60°	11.7	3.0
60°-70°	7.1	1.8
70°-80°	3.8	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	280.2	71.3
0°-40°	344.0	87.5
0°-60°	381.0	96.9
0°-90°	393.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	393.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	651	
5°	622	57
15°	425	117
25°	232	106
35°	100	64
45°	31	25
55°	13	12
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1262255

CATALOG NUMBER: P3AS09R259727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	650.7
1°	650.7
2°	647.6
3°	640.9
4°	632.3
5°	621.9
6°	608.4
7°	593.1
8°	575.3
9°	557.5
10°	538.6
11°	516.5
12°	493.8
13°	471.2
14°	448.5
15°	424.6
17.5°	368.2
20°	317.4
22.5°	271.4
25°	231.6
27.5°	194.2
30°	159.9
32.5°	128.7
35°	100.5
37.5°	76.6
40°	57.0
42.5°	41.7
45°	30.6
47.5°	23.3
50°	17.8
52.5°	14.7
55°	12.9
57.5°	11.0
60°	9.8
62.5°	8.0
65°	7.4
67.5°	6.1
70°	4.9
72.5°	4.3
75°	3.7
77.5°	3.1
80°	1.8
82.5°	1.2
85°	1.2
87.5°	0.6



TEST NUMBER: P1262255

CATALOG NUMBER: P3AS09R259727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)