

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263059

Luminaire Tested: P3AS17R359727DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263059
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359727DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1133.0 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263059

CATALOG NUMBER: P3AS17R359727DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1263059

CATALOG NUMBER: P3AS17R359727DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	571445
5°	549195
10°	478504
15°	366495
20°	245208
25°	148363
30°	85152
35°	47596
40°	25305
45°	13025
50°	6243
55°	4932
60°	4736
65°	3891
70°	4167
75°	3643
80°	4041
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13025 cd/sqm

TEST NUMBER: P1263059

CATALOG NUMBER: P3AS17R359727DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.0	20.0
10°-20°	439.9	38.8
20°-30°	288.0	25.4
30°-40°	116.8	10.3
40°-50°	35.0	3.1
50°-60°	11.9	1.1
60°-70°	8.0	0.7
70°-80°	4.7	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	954.9	84.3
0°-40°	1071.7	94.6
0°-60°	1118.7	98.7
0°-90°	1133.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1133.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2606	
5°	2495	227
15°	1614	440
25°	613	288
35°	178	117
45°	42	35
55°	13	12
65°	8	8
75°	4	5
85°	1	2
90°	0	

TEST NUMBER: P1263059

CATALOG NUMBER: P3AS17R359727DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2606.0
1°	2601.6
2°	2589.8
3°	2566.1
4°	2538.1
5°	2495.0
6°	2441.1
7°	2380.7
8°	2312.8
9°	2235.2
10°	2149.0
11°	2053.1
12°	1952.9
13°	1840.8
14°	1734.1
15°	1614.4
17.5°	1324.5
20°	1050.8
22.5°	808.3
25°	613.2
27.5°	457.0
30°	336.3
32.5°	246.8
35°	177.8
37.5°	126.1
40°	88.4
42.5°	61.4
45°	42.0
47.5°	28.0
50°	18.3
52.5°	14.0
55°	12.9
57.5°	11.9
60°	10.8
62.5°	9.7
65°	7.5
67.5°	6.5
70°	6.5
72.5°	5.4
75°	4.3
77.5°	3.2
80°	3.2
82.5°	2.2
85°	1.1
87.5°	1.1



TEST NUMBER: P1263059

CATALOG NUMBER: P3AS17R359727DE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)