

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262278

Luminaire Tested: P3AS09R309727DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262278
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309727DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 499.0 lumens
Efficiency: N/A
Efficacy: 45.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262278

CATALOG NUMBER: P3AS09R309727DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1262278

CATALOG NUMBER: P3AS09R309727DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	117885
5°	115232
10°	107168
15°	95369
20°	82024
25°	69488
30°	57680
35°	45240
40°	32432
45°	21274
50°	12110
55°	7952
60°	7499
65°	7005
70°	6283
75°	5676
80°	5430
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21274 cd/sqm

TEST NUMBER: P1262278

CATALOG NUMBER: P3AS09R309727DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.6	9.7
10°-20°	116.8	23.4
20°-30°	131.6	26.4
30°-40°	105.1	21.1
40°-50°	54.0	10.8
50°-60°	20.3	4.1
60°-70°	13.3	2.7
70°-80°	7.2	1.4
80°-90°	2.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	297.0	59.5
0°-40°	402.1	80.6
0°-60°	476.4	95.5
0°-90°	499.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	499.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	538	
5°	524	49
15°	420	117
25°	287	132
35°	169	105
45°	69	54
55°	21	20
65°	14	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1262278

CATALOG NUMBER: P3AS09R309727DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	537.6
1°	537.6
2°	535.8
3°	532.7
4°	528.4
5°	523.5
6°	517.4
7°	509.5
8°	500.9
9°	491.1
10°	481.3
11°	470.3
12°	458.6
13°	446.4
14°	433.5
15°	420.1
17.5°	385.8
20°	351.5
22.5°	318.4
25°	287.2
27.5°	256.6
30°	227.8
32.5°	198.4
35°	169.0
37.5°	140.2
40°	113.3
42.5°	89.4
45°	68.6
47.5°	50.8
50°	35.5
52.5°	25.1
55°	20.8
57.5°	19.0
60°	17.1
62.5°	15.3
65°	13.5
67.5°	11.6
70°	9.8
72.5°	8.0
75°	6.7
77.5°	5.5
80°	4.3
82.5°	3.1
85°	1.8
87.5°	0.6



TEST NUMBER: P1262278

CATALOG NUMBER: P3AS09R309727DE010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)