

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263102

Luminaire Tested: P3AS17R409727DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263102
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409727DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1256.0 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263102

CATALOG NUMBER: P3AS17R409727DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1263102

CATALOG NUMBER: P3AS17R409727DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	555767
5°	539620
10°	489681
15°	404543
20°	291809
25°	180494
30°	97711
35°	50514
40°	27451
45°	15381
50°	7710
55°	5773
60°	5219
65°	5033
70°	4809
75°	4575
80°	4041
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15381 cd/sqm

TEST NUMBER: P1263102

CATALOG NUMBER: P3AS17R409727DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.0	18.0
10°-20°	485.2	38.6
20°-30°	346.3	27.6
30°-40°	127.5	10.2
40°-50°	40.1	3.2
50°-60°	14.0	1.1
60°-70°	9.6	0.8
70°-80°	5.7	0.5
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1057.5	84.2
0°-40°	1185.0	94.3
0°-60°	1239.1	98.7
0°-90°	1256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2534	
5°	2452	226
15°	1782	485
25°	746	346
35°	189	127
45°	50	40
55°	15	14
65°	10	10
75°	5	6
85°	1	2
90°	0	

TEST NUMBER: P1263102

CATALOG NUMBER: P3AS17R409727DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2534.5
2.5°	2515.1
5°	2451.5
7.5°	2345.9
10°	2199.2
12.5°	2012.7
15°	1782.0
17.5°	1523.3
20°	1250.5
22.5°	982.1
25°	746.0
27.5°	547.7
30°	385.9
32.5°	270.6
35°	188.7
37.5°	133.7
40°	95.9
42.5°	69.0
45°	49.6
47.5°	33.4
50°	22.6
52.5°	16.2
55°	15.1
57.5°	14.0
60°	11.9
62.5°	10.8
65°	9.7
67.5°	8.6
70°	7.5
72.5°	6.5
75°	5.4
77.5°	4.3
80°	3.2
82.5°	2.2
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)