

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263168

Luminaire Tested: P3AS17R559727DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559727DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1391.0 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263168

CATALOG NUMBER: P3AS17R559727DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1263168

CATALOG NUMBER: P3AS17R559727DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	98	94	90	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	84	98	92	87	84	90	86	83		88	84	82		86
5	95	88	83	79	94	87	82	78	85	81	78		84	80	77		82
6	91	83	78	74	90	82	77	74	81	76	73		80	76	73		78
7	87	79	73	70	86	78	73	69	77	72	69		76	72	69		75
8	83	75	69	66	82	74	69	66	73	69	65		72	68	65		71
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68
10	77	68	62	59	76	67	62	59	67	62	59		66	62	59		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	403367
5°	389103
10°	402999
15°	397324
20°	367719
25°	297404
30°	178230
35°	60391
40°	16631
45°	7381
50°	2149
55°	421
60°	219
65°	259
70°	321
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7381 cd/sqm

TEST NUMBER: P1263168

CATALOG NUMBER: P3AS17R559727DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.0	12.3
10°-20°	487.3	35.0
20°-30°	541.7	38.9
30°-40°	168.6	12.1
40°-50°	20.3	1.5
50°-60°	1.6	0.1
60°-70°	0.5	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1200.0	86.3
0°-40°	1368.6	98.4
0°-60°	1390.4	100.0
0°-90°	1391.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1391.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1840	
5°	1768	171
15°	1750	487
25°	1229	542
35°	226	169
45°	24	20
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1263168

CATALOG NUMBER: P3AS17R559727DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1839.5
1°	1832.7
2°	1814.7
3°	1792.5
4°	1772.4
5°	1767.7
6°	1772.9
7°	1784.0
8°	1796.7
9°	1806.8
10°	1809.9
11°	1807.8
12°	1799.4
13°	1786.2
14°	1770.8
15°	1750.2
16°	1726.4
17°	1696.3
18°	1662.5
19°	1621.8
20°	1575.8
21°	1523.5
22°	1461.7
23°	1393.5
24°	1315.3
25°	1229.2
26°	1134.6
27°	1034.2
28°	926.9
29°	816.5
30°	703.9
31°	590.8
32°	480.4
32.5°	431.2
33°	380.5
34°	294.3
35°	225.6
36°	171.7
37°	127.4
37.5°	108.9
38°	94.6
39°	71.9
40°	58.1
42.5°	37.0
45°	23.8

TEST NUMBER: P1263168

CATALOG NUMBER: P3AS17R559727DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	14.3
50°	6.3
52.5°	2.1
55°	1.1
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)