

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262350

Luminaire Tested: P3AS09R459727DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262350
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459727DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 822.0 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262350

CATALOG NUMBER: P3AS09R459727DE010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1262350

CATALOG NUMBER: P3AS09R459727DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	90	89
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87	86	85
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	83	82	81
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	78	77
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	74	73
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	71	70
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	68	67
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	65	64
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	356375
5°	358287
10°	347266
15°	291012
20°	222456
25°	135419
30°	56338
35°	18042
40°	5611
45°	1147
50°	853
55°	956
60°	789
65°	934
70°	769
75°	1017
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1147 cd/sqm

TEST NUMBER: P1262350

CATALOG NUMBER: P3AS09R459727DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.5	18.7
10°-20°	352.3	42.9
20°-30°	253.7	30.9
30°-40°	52.8	6.4
40°-50°	4.8	0.6
50°-60°	2.0	0.2
60°-70°	1.6	0.2
70°-80°	1.0	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	759.5	92.4
0°-40°	812.3	98.8
0°-60°	819.1	99.7
0°-90°	822.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	822.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1625	
5°	1628	154
15°	1282	352
25°	560	254
35°	67	53
45°	4	5
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1262350

CATALOG NUMBER: P3AS09R459727DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1625.2
2.5°	1625.8
5°	1627.7
7.5°	1616.0
10°	1559.6
12.5°	1441.9
15°	1281.9
17.5°	1118.2
20°	953.3
22.5°	763.9
25°	559.7
27.5°	369.1
30°	222.5
32.5°	124.5
35°	67.4
37.5°	38.0
40°	19.6
42.5°	8.6
45°	3.7
47.5°	2.5
50°	2.5
52.5°	2.5
55°	2.5
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)