

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263372

Luminaire Tested: P3AS20R259727D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R259727D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 726.1 lumens
Efficiency: N/A
Efficacy: 25.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263372

CATALOG NUMBER: P3AS20R259727D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1263372

CATALOG NUMBER: P3AS20R259727D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	465708
5°	434491
10°	348067
15°	236256
20°	142952
25°	83594
30°	47602
35°	26180
40°	13912
45°	7319
50°	4264
55°	3173
60°	2719
65°	2906
70°	2693
75°	2372
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7319 cd/sqm

TEST NUMBER: P1263372

CATALOG NUMBER: P3AS20R259727D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.2	24.1
10°-20°	286.1	39.4
20°-30°	163.5	22.5
30°-40°	64.5	8.9
40°-50°	19.8	2.7
50°-60°	7.8	1.1
60°-70°	5.3	0.7
70°-80°	3.0	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	624.8	86.1
0°-40°	689.3	94.9
0°-60°	716.9	98.7
0°-90°	726.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	726.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2124	
5°	1974	175
15°	1041	286
25°	346	163
35°	98	65
45°	24	20
55°	8	8
65°	6	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1263372

CATALOG NUMBER: P3AS20R259727D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2123.8
1°	2119.6
2°	2102.3
3°	2071.7
4°	2029.4
5°	1973.9
6°	1908.7
7°	1835.1
8°	1749.8
9°	1662.4
10°	1563.2
11°	1465.3
12°	1357.8
13°	1251.6
14°	1142.7
15°	1040.7
17.5°	806.9
20°	612.6
22.5°	460.0
25°	345.5
27.5°	256.0
30°	188.0
32.5°	136.0
35°	97.8
37.5°	69.4
40°	48.6
42.5°	33.3
45°	23.6
47.5°	16.7
50°	12.5
52.5°	9.7
55°	8.3
57.5°	7.6
60°	6.2
62.5°	5.6
65°	5.6
67.5°	4.9
70°	4.2
72.5°	3.5
75°	2.8
77.5°	2.1
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.7



TEST NUMBER: P1263372

CATALOG NUMBER: P3AS20R259727D010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)