

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263378

Luminaire Tested: P3AS20R259727D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R259727D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 557.0 lumens
Efficiency: N/A
Efficacy: 19.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263378

CATALOG NUMBER: P3AS20R259727D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1263378

CATALOG NUMBER: P3AS20R259727D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132380
5°	129209
10°	119748
15°	106652
20°	91661
25°	77908
30°	64136
35°	49978
40°	35953
45°	22824
50°	13509
55°	9290
60°	8508
65°	7939
70°	7117
75°	6439
80°	6188
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22824 cd/sqm

TEST NUMBER: P1263378

CATALOG NUMBER: P3AS20R259727D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	9.8
10°-20°	130.4	23.4
20°-30°	147.4	26.5
30°-40°	116.6	20.9
40°-50°	58.9	10.6
50°-60°	23.6	4.2
60°-70°	15.1	2.7
70°-80°	8.3	1.5
80°-90°	2.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	332.2	59.6
0°-40°	448.8	80.6
0°-60°	531.2	95.4
0°-90°	557.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	557.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	604	
5°	587	54
15°	470	130
25°	322	147
35°	187	117
45°	74	59
55°	24	24
65°	15	15
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1263378

CATALOG NUMBER: P3AS20R259727D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	603.7
1°	603.7
2°	601.6
3°	598.1
4°	593.3
5°	587.0
6°	579.4
7°	570.4
8°	560.7
9°	549.6
10°	537.8
11°	524.6
12°	512.1
13°	497.5
14°	483.7
15°	469.8
17.5°	430.9
20°	392.8
22.5°	356.7
25°	322.0
27.5°	288.0
30°	253.3
32.5°	220.7
35°	186.7
37.5°	155.4
40°	125.6
42.5°	97.8
45°	73.6
47.5°	54.8
50°	39.6
52.5°	29.8
55°	24.3
57.5°	22.2
60°	19.4
62.5°	17.3
65°	15.3
67.5°	13.2
70°	11.1
72.5°	9.7
75°	7.6
77.5°	6.2
80°	4.9
82.5°	3.5
85°	2.1
87.5°	0.7



TEST NUMBER: P1263378

CATALOG NUMBER: P3AS20R259727D010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)