

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262447

Luminaire Tested: P3AS09R609727DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609727DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 644.0 lumens
Efficiency: N/A
Efficacy: 58.0 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262447

CATALOG NUMBER: P3AS09R609727DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1262447

CATALOG NUMBER: P3AS09R609727DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152071
5°	150627
10°	146245
15°	137004
20°	121274
25°	101449
30°	79506
35°	57688
40°	38358
45°	23909
50°	12929
55°	3747
60°	3508
65°	3165
70°	3142
75°	3135
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23909 cd/sqm

TEST NUMBER: P1262447

CATALOG NUMBER: P3AS09R609727DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.4	10.0
10°-20°	167.4	26.0
20°-30°	190.8	29.6
30°-40°	135.3	21.0
40°-50°	61.4	9.5
50°-60°	13.0	2.0
60°-70°	6.3	1.0
70°-80°	3.9	0.6
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.7	65.6
0°-40°	558.1	86.7
0°-60°	632.5	98.2
0°-90°	644.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	644.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	694	
5°	684	64
15°	604	167
25°	419	191
35°	216	135
45°	77	61
55°	10	13
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1262447

CATALOG NUMBER: P3AS09R609727DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	693.5
2.5°	691.0
5°	684.3
7.5°	672.7
10°	656.8
12.5°	634.1
15°	603.5
17.5°	565.0
20°	519.7
22.5°	470.7
25°	419.3
27.5°	366.6
30°	314.0
32.5°	263.8
35°	215.5
37.5°	172.6
40°	134.0
42.5°	101.6
45°	77.1
47.5°	57.5
50°	37.9
52.5°	17.8
55°	9.8
57.5°	8.6
60°	8.0
62.5°	7.3
65°	6.1
67.5°	5.5
70°	4.9
72.5°	4.3
75°	3.7
77.5°	3.1
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)