

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263402

Luminaire Tested: P3AS20R309727D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309727D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 97CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1787.0 lumens
Efficiency: N/A
Efficacy: 62.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263402
CATALOG NUMBER: P3AS20R309727D010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1263402
 CATALOG NUMBER: P3AS20R309727D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	86	85
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	82
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82	81	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	79	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	75	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1421794
5°	1403254
10°	1225161
15°	778733
20°	308540
25°	103046
30°	47957
35°	21737
40°	8330
45°	4093
50°	1194
55°	535
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4093 cd/sqm



TEST NUMBER: P1263402
 CATALOG NUMBER: P3AS20R309727D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	582.8	32.6
10°-20°	903.8	50.6
20°-30°	233.1	13.0
30°-40°	54.7	3.1
40°-50°	10.7	0.6
50°-60°	1.2	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1719.8	96.2
0°-40°	1774.5	99.3
0°-60°	1786.4	100.0
0°-90°	1787.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1787.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6484	
5°	6375	583
15°	3430	904
25°	426	233
35°	81	55
45°	13	11
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1263402
CATALOG NUMBER: P3AS20R309727D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	6483.9
1°	6479.0
2°	6463.8
3°	6446.4
4°	6420.8
5°	6375.0
6°	6300.8
7°	6177.3
8°	6008.7
9°	5788.8
10°	5502.3
11°	5161.7
12°	4789.9
13°	4361.9
14°	3913.8
15°	3430.3
16°	2956.5
17°	2500.0
18°	2062.3
19°	1660.7
20°	1322.2
21°	1040.5
22°	818.6
23°	647.9
24°	518.9
25°	425.9
26°	355.2
27°	301.8
28°	260.8
29°	223.4
30°	189.4
32.5°	119.3
35°	81.2
37.5°	50.6
40°	29.1
42.5°	19.4
45°	13.2
47.5°	7.6
50°	3.5
52.5°	1.4
55°	1.4
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7



TEST NUMBER: P1263402
CATALOG NUMBER: P3AS20R309727D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)