

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262476

Luminaire Tested: P3AS09R659727DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262476
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659727DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 614.0 lumens
Efficiency: N/A
Efficacy: 55.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262476

CATALOG NUMBER: P3AS09R659727DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1262476

CATALOG NUMBER: P3AS09R659727DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144791
5°	143055
10°	137628
15°	128922
20°	115953
25°	98473
30°	77025
35°	54877
40°	35924
45°	22204
50°	11258
55°	3976
60°	3508
65°	3476
70°	3142
75°	3135
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22204 cd/sqm

TEST NUMBER: P1262476

CATALOG NUMBER: P3AS09R659727DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.0	9.9
10°-20°	158.1	25.7
20°-30°	184.7	30.1
30°-40°	129.1	21.0
40°-50°	56.8	9.3
50°-60°	12.6	2.1
60°-70°	6.4	1.0
70°-80°	3.9	0.6
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	403.8	65.8
0°-40°	532.9	86.8
0°-60°	602.4	98.1
0°-90°	614.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	614.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	660	
5°	650	61
15°	568	158
25°	407	185
35°	205	129
45°	72	57
55°	10	13
65°	7	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1262476

CATALOG NUMBER: P3AS09R659727DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	660.3
2.5°	657.9
5°	649.9
7.5°	636.5
10°	618.1
12.5°	595.5
15°	567.9
17.5°	534.3
20°	496.9
22.5°	454.7
25°	407.0
27.5°	356.8
30°	304.2
32.5°	253.4
35°	205.0
37.5°	162.8
40°	125.5
42.5°	94.9
45°	71.6
47.5°	52.6
50°	33.0
52.5°	17.1
55°	10.4
57.5°	9.2
60°	8.0
62.5°	7.3
65°	6.7
67.5°	5.5
70°	4.9
72.5°	4.3
75°	3.7
77.5°	3.1
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)