

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262483

Luminaire Tested: P3AS09R659727DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262483
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659727DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 208.0 lumens
Efficiency: N/A
Efficacy: 18.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262483

CATALOG NUMBER: P3AS09R659727DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1262483

CATALOG NUMBER: P3AS09R659727DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52869
5°	51552
10°	48006
15°	43020
20°	37150
25°	30921
30°	24383
35°	18069
40°	12452
45°	7722
50°	4196
55°	2638
60°	2237
65°	2024
70°	1731
75°	1525
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7722 cd/sqm

TEST NUMBER: P1262483

CATALOG NUMBER: P3AS09R659727DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.8	10.5
10°-20°	52.7	25.3
20°-30°	58.3	28.0
30°-40°	42.3	20.3
40°-50°	19.8	9.5
50°-60°	6.7	3.2
60°-70°	3.9	1.9
70°-80°	2.0	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	132.7	63.8
0°-40°	175.0	84.1
0°-60°	201.5	96.9
0°-90°	208.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	208.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	241	
5°	234	22
15°	190	53
25°	128	58
35°	68	42
45°	25	20
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1262483

CATALOG NUMBER: P3AS09R659727DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	241.1
2.5°	239.6
5°	234.2
7.5°	226.1
10°	215.6
12.5°	203.3
15°	189.5
17.5°	174.5
20°	159.2
22.5°	143.3
25°	127.8
27.5°	111.9
30°	96.3
32.5°	81.3
35°	67.5
37.5°	54.9
40°	43.5
42.5°	33.3
45°	24.9
47.5°	18.0
50°	12.3
52.5°	8.4
55°	6.9
57.5°	6.0
60°	5.1
62.5°	4.5
65°	3.9
67.5°	3.3
70°	2.7
72.5°	2.4
75°	1.8
77.5°	1.5
80°	1.2
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)