

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262496

Luminaire Tested: P3AS09R709727DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262496
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709727DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 731.0 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262496
CATALOG NUMBER: P3AS09R709727DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1262496

CATALOG NUMBER: P3AS09R709727DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			79
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			57
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142138
5°	134030
10°	127074
15°	124791
20°	120294
25°	113402
30°	112574
35°	98056
40°	63433
45°	29988
50°	4196
55°	344
60°	263
65°	311
70°	192
75°	254
80°	379
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29988 cd/sqm



TEST NUMBER: P1262496
 CATALOG NUMBER: P3AS09R709727DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	7.8
10°-20°	154.4	21.1
20°-30°	218.4	29.9
30°-40°	219.5	30.0
40°-50°	78.9	10.8
50°-60°	2.1	0.3
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	429.6	58.8
0°-40°	649.1	88.8
0°-60°	730.2	99.9
0°-90°	731.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	731.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	648	
5°	609	57
15°	550	154
25°	469	218
35°	366	219
45°	97	79
55°	1	2
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1262496
CATALOG NUMBER: P3AS09R709727DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	648.2
1°	646.4
2°	640.7
3°	631.7
4°	620.3
5°	608.9
6°	598.1
7°	589.7
8°	582.2
9°	576.1
10°	570.7
11°	566.2
12°	562.0
13°	557.8
14°	553.9
15°	549.7
16°	544.6
17°	539.2
18°	532.6
19°	524.5
20°	515.5
21°	505.6
22°	495.7
23°	486.1
24°	476.8
25°	468.7
26°	463.0
27°	458.5
28°	454.9
29°	450.6
30°	444.6
31°	435.9
32°	423.6
32.5°	416.7
33°	407.4
34°	389.1
35°	366.3
36°	341.1
37°	312.5
37.5°	299.3
38°	281.3
39°	249.2
40°	221.6
42.5°	153.4
45°	96.7



TEST NUMBER: P1262496
CATALOG NUMBER: P3AS09R709727DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	51.9
50°	12.3
52.5°	1.5
55°	0.9
57.5°	0.9
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)