

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262511

Luminaire Tested: P3AS09R709727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262511
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 440.0 lumens
Efficiency: N/A
Efficacy: 39.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262511

CATALOG NUMBER: P3AS09R709727DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1262511

CATALOG NUMBER: P3AS09R709727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103215
5°	101320
10°	95523
15°	86697
20°	75840
25°	63971
30°	52388
35°	40636
40°	29083
45°	18421
50°	9177
55°	5620
60°	4824
65°	4462
70°	3911
75°	3643
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18421 cd/sqm

TEST NUMBER: P1262511

CATALOG NUMBER: P3AS09R709727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.9	9.8
10°-20°	106.3	24.2
20°-30°	121.0	27.5
30°-40°	94.6	21.5
40°-50°	46.5	10.6
50°-60°	14.3	3.2
60°-70°	8.5	1.9
70°-80°	4.5	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.2	61.4
0°-40°	364.9	82.9
0°-60°	425.7	96.8
0°-90°	440.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	440.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	471	
5°	460	43
15°	382	106
25°	264	121
35°	152	95
45°	59	46
55°	15	14
65°	9	8
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1262511

CATALOG NUMBER: P3AS09R709727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	470.7
2.5°	468.2
5°	460.3
7.5°	447.4
10°	429.0
12.5°	407.6
15°	381.9
17.5°	354.4
20°	325.0
22.5°	294.4
25°	264.4
27.5°	235.0
30°	206.9
32.5°	178.7
35°	151.8
37.5°	126.1
40°	101.6
42.5°	79.0
45°	59.4
47.5°	41.6
50°	26.9
52.5°	17.7
55°	14.7
57.5°	12.9
60°	11.0
62.5°	9.8
65°	8.6
67.5°	7.3
70°	6.1
72.5°	4.9
75°	4.3
77.5°	3.7
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)