

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263446

Luminaire Tested: P3AS20R359727D010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R359727D010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 918.0 lumens
Efficiency: N/A
Efficacy: 31.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263446
CATALOG NUMBER: P3AS20R359727D010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1263446
 CATALOG NUMBER: P3AS20R359727D010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	295064
5°	287805
10°	263121
15°	223338
20°	176789
25°	133725
30°	97357
35°	65826
40°	40447
45°	23227
50°	13987
55°	11354
60°	9911
65°	8821
70°	7245
75°	7202
80°	7198
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23227 cd/sqm



TEST NUMBER: P1263446
 CATALOG NUMBER: P3AS20R359727D010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.8	13.2
10°-20°	271.2	29.5
20°-30°	253.7	27.6
30°-40°	155.3	16.9
40°-50°	61.2	6.7
50°-60°	26.9	2.9
60°-70°	16.8	1.8
70°-80°	9.0	1.0
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	645.8	70.3
0°-40°	801.0	87.3
0°-60°	889.2	96.9
0°-90°	918.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	918.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1346	
5°	1308	121
15°	984	271
25°	553	254
35°	246	155
45°	75	61
55°	30	27
65°	17	17
75°	8	9
85°	3	3
90°	0	



TEST NUMBER: P1263446
CATALOG NUMBER: P3AS20R359727D010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1345.6
1°	1347.0
2°	1342.8
3°	1334.3
4°	1321.6
5°	1307.5
6°	1289.1
7°	1267.9
8°	1242.4
9°	1214.2
10°	1181.7
11°	1147.7
12°	1111.0
13°	1071.4
14°	1027.6
15°	983.8
17.5°	870.7
20°	757.6
22.5°	648.8
25°	552.7
27.5°	463.6
30°	384.5
32.5°	311.0
35°	245.9
37.5°	188.0
40°	141.3
42.5°	101.8
45°	74.9
47.5°	53.7
50°	41.0
52.5°	33.9
55°	29.7
57.5°	25.4
60°	22.6
62.5°	19.8
65°	17.0
67.5°	14.1
70°	11.3
72.5°	9.9
75°	8.5
77.5°	7.1
80°	5.7
82.5°	4.2
85°	2.8
87.5°	1.4



TEST NUMBER: P1263446
CATALOG NUMBER: P3AS20R359727D010 E3DLP1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)