

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263468

Luminaire Tested: P3AS20R409727D010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409727D010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1040.0 lumens
Efficiency: N/A
Efficacy: 36.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263468
CATALOG NUMBER: P3AS20R409727D010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1263468
 CATALOG NUMBER: P3AS20R409727D010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80				80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74				74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69				69
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65				65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	62	61				61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58				58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54				54
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	323834
5°	317279
10°	295408
15°	257459
20°	207498
25°	155525
30°	109359
35°	71634
40°	43367
45°	25894
50°	15454
55°	12463
60°	11183
65°	9547
70°	9104
75°	7202
80°	7198
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25894 cd/sqm



TEST NUMBER: P1263468
 CATALOG NUMBER: P3AS20R409727D010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.9	12.9
10°-20°	312.4	30.0
20°-30°	294.4	28.3
30°-40°	170.2	16.4
40°-50°	67.8	6.5
50°-60°	30.0	2.9
60°-70°	18.6	1.8
70°-80°	9.7	0.9
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	740.6	71.2
0°-40°	910.8	87.6
0°-60°	1008.7	97.0
0°-90°	1040.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1040.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1477	
5°	1441	134
15°	1134	312
25°	643	294
35°	268	170
45°	84	68
55°	33	30
65°	18	19
75°	8	10
85°	3	3
90°	0	



TEST NUMBER: P1263468
CATALOG NUMBER: P3AS20R409727D010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1476.8
2.5°	1468.3
5°	1441.4
7.5°	1391.8
10°	1326.7
12.5°	1238.9
15°	1134.1
17.5°	1016.6
20°	889.2
22.5°	761.8
25°	642.8
27.5°	532.4
30°	431.9
32.5°	344.1
35°	267.6
37.5°	202.5
40°	151.5
42.5°	113.3
45°	83.5
47.5°	60.9
50°	45.3
52.5°	36.8
55°	32.6
57.5°	29.7
60°	25.5
62.5°	21.2
65°	18.4
67.5°	15.6
70°	14.2
72.5°	11.3
75°	8.5
77.5°	7.1
80°	5.7
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)